

# High profile ball transfer unit




## BPLF

## For light loads

- **Pressed steel ball transfer unit with mounting plate**
- With 2 or 4 mounting holes for screws or rivets.  
(The BPLF25-55-2F has 2 slots rather than 2 holes to accommodate different centre distances)
- For light loads
- Housing made from pressed steel
- With drainage hole and felt seal.
- Orientation: horizontal with ball upwards
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:



**BPL:**galvanised steel body and steel balls  
**BPL/SS:**stainless steel body and stainless steel balls



### DISCOUNTS

| Qty   | 1+   | 6+   | 20+  | 40+  | 60+        |
|-------|------|------|------|------|------------|
| Disc. | Prix | -10% | -15% | -20% | On request |

| Part number   | Ødw<br>ball | ØA   | B    | C   | D              | E              | F                     | Carrying<br>capacity<br>(kg) | Weight<br>(kg) | Stock* | Price<br>each<br>1 to 5 |
|---|-------------|------|------|-----|----------------|----------------|-----------------------|------------------------------|----------------|--------|-------------------------|
| <b>Steel body, steel balls</b>                      |             |      |      |     |                |                |                       |                              |                |        |                         |
| BPLF25-45-2F  | 25,4        | 45,0 | 30,4 | 6,3 | 69 x 51        | 55,9 -<br>60,3 | slot<br>2 x 5,5 x 7,7 | 55                           | 0,155          | ✓      | 7,53 €                  |
| BPLF38-67-4   | 38,1        | 66,9 | 46,2 | 9,8 | 76,2 x<br>76,2 | 62,7 x<br>62,7 | 4 x Ø7,1              | 115                          | 0,520          | -      | 22,79 €                 |
| <b>Stainless steel body / Stainless steel balls</b> |             |      |      |     |                |                |                       |                              |                |        |                         |
| BPLF25-45-2F/SS                                     | 25,4        | 45,0 | 30,4 | 6,3 | 69 x<br>51     | 55,9 -<br>60,3 | slot<br>2 x 5,5 x 7,7 | 55                           | 0,151          | ✓      | 19,64 €                 |

\*Depending on availability - Dimensions in mm

- Pressed steel ball transfer unit
- With 2 fixing holes for screws or rivets
- For light loads
- Housing made from pressed sheet metal
- With drainage hole and felt seal.
- Orientation: horizontal with ball upwards
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:




**BPL:**galvanised steel body and steel balls

**BPL/SS:** stainless steel body and steel balls  
stainless steel 420

### Advantages

- Ideal for small applications with small space requirements



### DISCOUNTS

| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
|-------|-----|------|------|------|------------|
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number   | Ødw  | ball ØA | B    | C   | ØD   | E    | F   | ØG   | ØH      | Carrying capacity (kg) | Weight (g) | Price each 1 to 5 | Stock*  |
|---|------|---------|------|-----|------|------|-----|------|---------|------------------------|------------|-------------------|---------|
|   |      |         |      |     |      |      |     |      |         |                        |            |                   | ✓       |
| <b>Steel body, steel balls</b>                      |      |         |      |     |      |      |     |      |         |                        |            |                   |         |
| BPL15-41  | 15,0 | 41,0    | 10,8 | 5,0 | 24,0 | 8,5  | 3,2 | 30,0 | 2 x 3,4 | 15                     | 0,045      | ✓                 | 5,46 €  |
| BPL19-61  | 19,0 | 61,0    | 10,0 | 3,2 | 29,1 | 12,0 | 3,2 | 44,5 | 2 x 5,1 | 25                     | 0,090      | ✓                 | 5,32 €  |
| BPL25-73  | 25,4 | 73,0    | 14,2 | 6,3 | 37,2 | 15,8 | 3,5 | 55,6 | 2 x 5,1 | 55                     | 0,170      | ✓                 | 7,19 €  |
| BPL25-56  | 25,0 | 56,0    | 14,6 | 7,8 | 36,0 | 15,4 | 3,3 | 45,0 | 2 x 4,0 | 60                     | 0,125      | ✓                 | 7,71 €  |
| BPL32-73  | 32,0 | 73,7    | 16,2 | 8,0 | 45,5 | 19,9 | 4,2 | 58,7 | 2 x 5,1 | 125                    | 0,269      | ✓                 | 11,86 € |
| <b>Stainless steel body / Stainless steel balls</b> |      |         |      |     |      |      |     |      |         |                        |            |                   |         |
| BPL19-61/SS   | 19,0 | 61,0    | 10,0 | 3,2 | 29,1 | 12,0 | 3,2 | 44,5 | 2 x 5,1 | 25                     | 0,086      | ✓                 | 13,41 € |
| BPL25-73/SS   | 25,4 | 73,0    | 14,2 | 6,3 | 37,2 | 15,8 | 3,5 | 55,6 | 2 x 5,1 | 55                     | 0,172      | -                 | 19,41 € |
| BPL32-73/SS   | 32,0 | 73,7    | 16,2 | 8,0 | 45,5 | 19,9 | 4,2 | 58,7 | 2 x 5,1 | 125                    | 0,256      | ✓                 | 26,70 € |

\* Depending on availability - Dimensions in mm

# Flange mounting ball transfer unit Stock

## BPPE

## Plastic

- **Plastic ball mounting ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- Clips compensate for irregularities in seat bore diameter
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:  
Acetal body and balls (POM)




### Advantages

- Resists salt water and chemical attacks
- Non-conductive and non-magnetic
- Suitable for antimicrobial applications
- For use in chemical, pharmaceutical and medical applications

### Accessory

- BPHFC<sub>CLIP</sub>, clip for ball transfer unit (tome 5 p.43)



### DISCOUNTS

|       |     |      |      |      |            |
|-------|-----|------|------|------|------------|
| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number  | Ødw<br>ball | ØA | B    | C   | ØD | E    | Carrying<br>capacity<br>(kg) | Weight<br>(g) | Stock* | Price each |
|--------------|-------------|----|------|-----|----|------|------------------------------|---------------|--------|------------|
|              |             |    |      |     |    |      |                              |               |        | 1 to 5     |
| BPPE15-24/PP | 15          | 24 | 8,0  | 4,8 | 30 | 20,0 | 7                            | 0,010         | ✓      | 24,08 €    |
| BPPE22-36/PP | 22          | 36 | 9,8  | 4,5 | 45 | 30,5 | 10                           | 0,035         | ✓      | 36,11 €    |
| BPPE30-45/PP | 30          | 45 | 13,8 | 5,8 | 55 | 37,0 | 15                           | 0,065         | ✓      | 43,00 €    |
| BPPE45-62/PP | 45          | 62 | 19,0 | 8,5 | 75 | 53,5 | 20                           | 0,182         | -      | 95,27 €    |

\*Depending on availability. All dimensions in mm.

- **Pressed steel ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- For light loads
- Housing made from pressed steel
- Orientation: horizontal with ball upwards
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:

**BPL** : galvanized steel body and steel balls

**BPL/SS** : stainless steel body and steel balls




### Advantages

- Optional clips compensate for irregularities in seat bore diameter

### Accessory

- BPHFCUP, clip for ball transfer unit (tome 5 p.49)



### DISCOUNTS

| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
|-------|-----|------|------|------|------------|
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number  | Ødw<br>ball | ØA | B    | C   | ØD | E    | F   | Carrying<br>capacity<br>(kg) | Weight<br>(g) | Stock* | Price each<br>1 to 5 |
|--|-------------|----|------|-----|----|------|-----|------------------------------|---------------|--------|----------------------|
|  |             |    |      |     |    |      |     |                              |               |        |                      |
| <b>Steel body, steel balls</b>                     |             |    |      |     |    |      |     |                              |               |        |                      |
| BPLE15-24  | 15          | 24 | 9,5  | 4,6 | 31 | 21,0 | 2,8 | 60                           | 0,041         | ✓      | 4,69 €               |
| BPLE22-36  | 22          | 36 | 9,8  | 3,9 | 45 | 29,5 | 2,9 | 160                          | 0,128         | ✓      | 8,62 €               |
| BPLE30-45  | 30          | 45 | 13,8 | 6,8 | 55 | 37,0 | 3,6 | 280                          | 0,253         | ✓      | 13,01 €              |
| BPLE45-62  | 45          | 62 | 19,0 | 9,0 | 75 | 53,5 | 4,0 | 600                          | 0,720         | -      | 63,08 €              |
| <b>Stainless steel body, stainless steel balls</b> |             |    |      |     |    |      |     |                              |               |        |                      |
| BPLE15-24/SS                                       | 15          | 24 | 9,5  | 4,6 | 31 | 21,0 | 2,8 | 40                           | 0,039         | ✓      | 14,49 €              |
| BPLE22-36/SS                                       | 22          | 36 | 9,8  | 3,9 | 45 | 29,5 | 2,9 | 90                           | 0,125         | ✓      | 25,12 €              |
| BPLE30-45/SS                                       | 30          | 45 | 13,8 | 6,8 | 55 | 37,0 | 3,6 | 200                          | 0,271         | ✓      | 56,09 €              |
| BPLE45-62/SS                                       | 45          | 62 | 19,0 | 9,0 | 75 | 53,5 | 4,0 | 260                          | 0,710         | -      | 152,24 €             |

All dimensions in mm. \*Depending on availability

# Flush fitting ball transfer unit with flange

Stock

## BPHF

## For heavy loads

- Carrying ball for handling solid body
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:

**BPHF:**galvanised steel body and chromed steel ball

**BPHF/AS:**galvanised steel body and 420 stainless steel balls

**BPHF-SS:**body, components and balls- 420 stainless steels




### Advantages

- Good resistance to shocks
- Optional clips compensate for irregularities in seat bore diameter

### Accessory

- BPHF<sub>CLIP</sub>, clip for ball transfer unit (tome 5 p.49)



### DISCOUNTS

| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
|-------|-----|------|------|------|------------|
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number  | Ødw ball | ØA | B    | C   | ØD | E    | Carrying capacity (kg) | Weight (g) | Stock* | Price each 1 to 5 |
|--|----------|----|------|-----|----|------|------------------------|------------|--------|-------------------|
| <b>Steel body, steel balls</b>                     |          |    |      |     |    |      |                        |            |        |                   |
| BPHF15-24  | 15       | 24 | 9,5  | 4,0 | 31 | 21,0 | 60                     | 0,059      | ✓      | 6,34 €            |
| BPHF22-36  | 22       | 36 | 9,8  | 3,8 | 45 | 30,5 | 180                    | 0,189      | ✓      | 12,38 €           |
| BPHF30-45  | 30       | 45 | 13,8 | 5,8 | 55 | 36,8 | 350                    | 0,360      | ✓      | 19,60 €           |
| BPHF45-62  | 45       | 62 | 19,0 | 9,0 | 75 | 53,5 | 600                    | 1,010      | ✓      | 63,42 €           |
| <b>Steel body, stainless steel balls</b>           |          |    |      |     |    |      |                        |            |        |                   |
| BPHF15-24/AS                                       | 15       | 24 | 9,5  | 4,0 | 31 | 21,0 | 50                     | 0,059      | ✓      | 7,91 €            |
| BPHF22-36/AS                                       | 22       | 36 | 9,8  | 3,8 | 45 | 30,5 | 180                    | 0,188      | ✓      | 13,72 €           |
| BPHF30-45/AS                                       | 30       | 45 | 13,8 | 5,8 | 55 | 36,8 | 350                    | 0,357      | ✓      | 24,04 €           |
| BPHF45-62/AS                                       | 45       | 62 | 19,0 | 9,0 | 75 | 53,5 | 600                    | 1,000      | -      | 83,48 €           |
| <b>Stainless steel body, stainless steel balls</b> |          |    |      |     |    |      |                        |            |        |                   |
| BPHF15-24/SS                                       | 15       | 24 | 9,5  | 4,0 | 31 | 21,0 | 40                     | 0,058      | ✓      | 21,62 €           |
| BPHF22-36/SS                                       | 22       | 36 | 9,8  | 3,8 | 45 | 30,5 | 126                    | 0,188      | ✓      | 70,28 €           |
| BPHF30-45/SS                                       | 30       | 45 | 13,8 | 5,8 | 55 | 36,8 | 220                    | 0,357      | ✓      | 68,69 €           |
| BPHF45-62/SS                                       | 45       | 62 | 19,0 | 9,0 | 75 | 53,5 | 350                    | 1,020      | -      | 169,05 €          |

All dimensions in mm. \*Depending on availability

- **Ball transfer unit with solid body**
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:


**BPHT:**galvanised steel body and chromed steel balls

**BPHT/AS:**galvanised steel body and 420 stainless steel balls



### Advantages

- Good resistance to shocks



### DISCOUNTS

|              |     |      |      |      |            |
|--------------|-----|------|------|------|------------|
| <b>Qty</b>   | 1+  | 6+   | 20+  | 40+  | 60+        |
| <b>Disc.</b> | Net | -10% | -15% | -20% | On request |

| Part number                              | Ødw ball | ØA | B     | C    | D   | E    | ØF         | Carrying capacity (kg) | Weight (kg) | Stock* | Price each 1 to 5 |
|--|----------|----|-------|------|-----|------|------------|------------------------|-------------|--------|-------------------|
| <b>Steel body, steel balls</b>           |          |    |       |      |     |      |            |                        |             |        |                   |
| BPHT15-25                                | 15       | 25 | 46    | 26,0 | 5   | 20,0 | M8x1,25    | 60                     | 0,083       | ✓      | 14,54 €           |
| BPHT22-36                                | 22       | 36 | 62,9  | 37,5 | 4,5 | 25,4 | M12 x 1,75 | 180                    | 0,256       | ✓      | 22,73 €           |
| BPHT30-45                                | 30       | 45 | 69,2  | 43,8 | 6,5 | 25,4 | M12 x 1,75 | 350                    | 0,440       | ✓      | 29,05 €           |
| BPHT45-62                                | 45       | 62 | 107,3 | 66,0 | 8,5 | 41,3 | M20 x 2,5  | 600                    | 1,360       | -      | 105,24 €          |
| <b>Steel body, stainless steel balls</b> |          |    |       |      |     |      |            |                        |             |        |                   |
| BPHT15-25/AS                             | 15       | 25 | 46    | 26,0 | 5   | 20,0 | M8x1,25    | 50                     | 0,083       | ✓      | 15,31 €           |
| BPHT22-36/AS                             | 22       | 36 | 62,9  | 37,5 | 4,5 | 25,4 | M12 x 1,75 | 180                    | 0,256       | ✓      | 24,04 €           |
| BPHT30-45/AS                             | 30       | 45 | 69,2  | 43,8 | 6,5 | 25,4 | M12 x 1,75 | 350                    | 0,430       | ✓      | 31,69 €           |
| BPHT45-62/AS                             | 45       | 62 | 107,3 | 66,0 | 8,5 | 41,3 | M20 x 2,5  | 600                    | 1,350       | -      | 128,01 €          |

All dimensions in mm. \*Depending on availability

# Cylindrical flush fitting ball transfer unit

## BPH


## For heavy loads

- Flush fitting ball transfer unit with flange
- For heavy loads
- Carrying ball for handling solid body
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:
  - BPH:** galvanised steel body and chromed steel ball
  - BPH/AS:** galvanised steel body and 420 stainless steel balls



### Advantages

- Good resistance to shocks



### DISCOUNTS

| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
|-------|-----|------|------|------|------------|
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number                              | Ødw ball | ØA | B    | C    | D   | Carrying capacity (kg) | Weight (g) | Price each 1 to 5 |
|--|----------|----|------|------|-----|------------------------|------------|-------------------|
| <b>Steel body, steel balls</b>           |          |    |      |      |     |                        |            |                   |
| BPH15-24                                 | 15       | 24 | 20,0 | 15,0 | 5,0 | 60                     | 0,049      | 9,49 €            |
| BPH22-36                                 | 22       | 36 | 30,5 | 26,0 | 4,5 | 180                    | 0,177      | 12,39 €           |
| BPH30-45                                 | 30       | 45 | 36,8 | 30,3 | 6,5 | 350                    | 0,335      | 18,50 €           |
| BPH45-62                                 | 45       | 62 | 53,5 | 45,0 | 8,5 | 600                    | 0,940      | 55,47 €           |
| <b>Steel body, stainless steel balls</b> |          |    |      |      |     |                        |            |                   |
| BPH15-24/AS                              | 15       | 24 | 20,0 | 15,0 | 5,0 | 50                     | 0,048      | 11,59 €           |
| BPH22-36/AS                              | 22       | 36 | 30,5 | 26,0 | 4,5 | 180                    | 0,178      | 14,80 €           |
| BPH30-45/AS                              | 30       | 45 | 36,8 | 30,3 | 6,5 | 350                    | 0,338      | 21,37 €           |
| BPH45-62/AS                              | 45       | 62 | 53,5 | 45,0 | 8,5 | 600                    | 0,970      | 81,88 €           |

All dimensions in mm



# Spring loaded ball transfer unit

For heavy loads


BPHRF

- **Ball transfer unit with solid body**
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:  
Galvanised steel body and chromed steel balls



## Advantages

- Good resistance to shocks



## DISCOUNTS

|       |     |      |      |      |            |
|-------|-----|------|------|------|------------|
| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number | Ødw<br>ball | ØA   | B     | ØC | D    | E    | Carrying<br>capacity<br>(kg) | Deflection | Load<br>at max<br>deflection | Price each |
|-------------|-------------|------|-------|----|------|------|------------------------------|------------|------------------------------|------------|
|             |             |      |       |    |      |      |                              |            |                              | 1 to 5     |
| BPHRF22-39  | 22          | 39,0 | 58,0  | 50 | 14,0 | 53,5 | 70                           | 4,5        | 90                           | 90,20 €    |
| BPHRF30-48  | 30          | 48,5 | 70,0  | 62 | 17,5 | 63,0 | 135                          | 7,0        | 170                          | 142,18 €   |
| BPHRF45-66  | 45          | 66,5 | 100,5 | 85 | 25,5 | 90,0 | 230                          | 10,5       | 290                          | 185,91 €   |

All dimensions in mm

# Spring loaded ball transfer unit




## BPHR

## For heavy loads

- **Ball transfer unit with solid body**
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:  
Galvanised steel body and chromed steel balls

### Advantages

- Good resistance to shocks



### DISCOUNTS

|       |     |      |      |      |            |
|-------|-----|------|------|------|------------|
| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number | Ødw<br>ball | ØA   | B  | ØC   | D    | E    | Carrying<br>capacity<br>(kg) | Deflection | Load at max | Price each |
|-------------|-------------|------|----|------|------|------|------------------------------|------------|-------------|------------|
|             |             |      |    |      |      |      |                              |            | deflection  |            |
| BPHR12-24   | 12,7        | 23,9 | 30 | 24,5 | 28,5 | 10,5 | 40                           | 1,5        | 90          | 70,96 €    |
| BPHR16-30   | 15,8        | 29,9 | 36 | 30,5 | 34,5 | 10,5 | 60                           | 1,5        | 110         | 101,66 €   |
| BPHR25-40   | 25,4        | 39,8 | 48 | 40,5 | 46,5 | 10,5 | 100                          | 1,5        | 175         | 127,23 €   |
| BPHR30-50   | 30,0        | 49,9 | 60 | 50,5 | 58,5 | 12,3 | 335                          | 1,5        | 585         | 258,29 €   |


All dimensions in mm

- Mounting clip for barrel shaped ball transfer units
- Compensates for irregularities in size and diameter
- Ideal for where there is only access to one side of the mounting surface
- When using mounting clips, the diameter and height will change. For effective retention, a plate thickness of at least 3 mm is required



### Mounting

- 1 Install the clip in the bore
- 2 Push the ball unit through the clip
- 3 The external tabs extend and grip the shaft of the supporting ball



Typical application

### DISCOUNTS

| Qty   | 1+  | 6+   | 20+  | 40+  | 60+        |
|-------|-----|------|------|------|------------|
| Disc. | Net | -10% | -15% | -20% | On request |

| Part number                        | ØA | Ø Bore min/max | Additional height | For ball unit            | Stock* | Price each 1 to 5 |
|------------------------------------|----|----------------|-------------------|--------------------------|--------|-------------------|
| <b>Steel clip</b>                  |    |                |                   |                          |        |                   |
| BPHF15-CLIP                        | 24 | 25,0 - 25,5    | +0,3              | BPHF15 - BPLE15 - BPPE15 | ✓      | 1,81 €            |
| BPHF22-CLIP                        | 36 | 37,0 - 37,5    | +0,3              | BPHF22 - BPLE22 - BPPE22 | ✓      | 2,15 €            |
| BPHF30-CLIP                        | 45 | 46,0 - 46,5    | +0,3              | BPHF30 - BPLE30 - BPPE30 | ✓      | 2,21 €            |
| BPHF45-CLIP                        | 62 | 63,0 - 63,5    | +0,3              | BPHF45 - BPLE45 - BPPE45 | -      | 2,55 €            |
| <b>Stainless steel fixing clip</b> |    |                |                   |                          |        |                   |
| BPHF15-CLIP/SS                     | 24 | 25,0 - 25,5    | +0,3              | BPHF15 - BPLE15 - BPPE15 | -      | 2,25 €            |
| BPHF22-CLIP/SS                     | 36 | 37,0 - 37,5    | +0,3              | BPHF22 - BPLE22 - BPPE22 | -      | 2,60 €            |
| BPHF30-CLIP/SS                     | 45 | 46,0 - 46,5    | +0,3              | BPHF30 - BPLE30 - BPPE30 | -      | 3,47 €            |

\*Depending on availability - Dimensions in mm

- **Ball caster for positioning and aligning parts**
- The ball rolls durably on the sliding bearing
- The surface of the part is preserved
- Working temperature: -50°C to +90°C
- The load capacity decreases linearly at temperatures > 20°C.  
(Example: at 90°C, the load capacity is 60% max.)
- Materials:  
Burnished steel screw and steel ball bearing  
Plain bearing: polyurethane





### Applications

- Enables low-friction guidance
- ⚠ **Not suitable for indexing!**

### Advantage

- Adjusting the position of the carrier ball from the rear.



Typical application

### DISCOUNTS

|              |       |      |      |      |            |
|--------------|-------|------|------|------|------------|
| <b>Qty</b>   | 1+    | 6+   | 20+  | 40+  | 60+        |
| <b>Disc.</b> | Price | -10% | -15% | -20% | On request |

| Part number | ØD1 | L1 | Ball |     | Max. tightening torque (Nm) | Max load capacity for static use (N) | Weight (g) | Price each 1 to 5 |
|-------------|-----|----|------|-----|-----------------------------|--------------------------------------|------------|-------------------|
|             |     |    | ØD   | SW  |                             |                                      |            |                   |
| BPVM6-8     | M6  | 8  | 2,5  | 1,5 | 0,1                         | 172                                  | 1          | 14,87 €           |
| BPVM6-16    | M6  | 16 | 2,5  | 1,5 | 0,1                         | 172                                  | 3          | 14,87 €           |
| BPVM8-10    | M8  | 10 | 3,5  | 1,5 | 0,3                         | 336                                  | 3          | 14,96 €           |
| BPVM8-20    | M8  | 20 | 3,5  | 1,5 | 0,3                         | 336                                  | 7          | 14,96 €           |
| BPVM10-12   | M10 | 12 | 4,5  | 2,0 | 0,6                         | 556                                  | 5          | 15,08 €           |
| BPVM10-25   | M10 | 25 | 4,5  | 2,0 | 0,6                         | 556                                  | 13         | 15,08 €           |
| BPVM12-16   | M12 | 16 | 6,5  | 2,5 | 1,4                         | 1161                                 | 10         | 16,59 €           |
| BPVM12-35   | M12 | 35 | 6,5  | 2,5 | 1,4                         | 1161                                 | 27         | 16,59 €           |
| BPVM16-20   | M16 | 20 | 8,5  | 3,0 | 3,2                         | 1986                                 | 24         | 18,91 €           |
| BPVM16-50   | M16 | 50 | 8,5  | 3,0 | 3,2                         | 1986                                 | 71         | 18,91 €           |

Dimensions in mm

- **Ball caster for positioning and orienting parts**
- The ball rolls durably on the sliding bearing
- The surface of the part is preserved
- Working temperature: -50°C to +90°C
- The load capacity decreases linearly at temperatures > 20°C..  
(Example: at 90°C, the load capacity is 60% max.)

- Materials:

Screw stainless steel 303 hardened stainless steel ball



Plain bearing: polyurethane

### Applications

- Enables low-friction guidance
- ⚠ **Not suitable for indexing!**

### Advantage

- Adjusting the position of the carrier ball from the rear.



Typical application

### DISCOUNTS

| Qty   | 1+         | 6+   | 20+  | 40+ | 60+        |
|-------|------------|------|------|-----|------------|
| Disc. | Price -10% | -15% | -20% |     | On request |

| Part number  | ØD1 | L1 | Ball |     | Max. tightening torque (Nm) | Max load capacity for static use (N) | Weight (g) | Price each 1 to 5 |
|--------------|-----|----|------|-----|-----------------------------|--------------------------------------|------------|-------------------|
|              |     |    | ØD   | SW  |                             |                                      |            |                   |
| BPVM6-8/SS   | M6  | 8  | 2,5  | 1,5 | 0,1                         | 172                                  | 1          | 20,85 €           |
| BPVM6-16/SS  | M6  | 16 | 2,5  | 1,5 | 0,1                         | 172                                  | 3          | 20,85 €           |
| BPVM8-10/SS  | M8  | 10 | 3,5  | 1,5 | 0,3                         | 336                                  | 3          | 20,98 €           |
| BPVM8-20/SS  | M8  | 20 | 3,5  | 1,5 | 0,3                         | 336                                  | 7          | 20,98 €           |
| BPVM10-12/SS | M10 | 12 | 4,5  | 2,0 | 0,6                         | 556                                  | 5          | 21,12 €           |
| BPVM10-25/SS | M10 | 25 | 4,5  | 2,0 | 0,6                         | 556                                  | 13         | 21,12 €           |
| BPVM12-16/SS | M12 | 16 | 6,5  | 2,5 | 1,4                         | 1161                                 | 10         | 22,07 €           |
| BPVM12-35/SS | M12 | 35 | 6,5  | 2,5 | 1,4                         | 1161                                 | 27         | 22,07 €           |
| BPVM16-20/SS | M16 | 20 | 8,5  | 3,0 | 3,2                         | 1986                                 | 24         | 26,49 €           |
| BPVM16-50/SS | M16 | 50 | 8,5  | 3,0 | 3,2                         | 1986                                 | 71         | 26,49 €           |

Dimensions in mm

## BPPL

## For countersinking

- **Plain bearing ball caster**
- Maintenance free
- Working temperature: -50°C to +90°C
- The load capacity decreases linearly at temperatures > 20°C.  
(Example: at 90°C, the load capacity is 60% max.)
- Materials:
  - Case: Stainless steel
  - Plan bearing: polyurethane
  - Ball: Hardened stainless steel



### Advantage



- The knurled outside allows easy fitting into the holes of additional preparation.

### Assembly

- Fastening is done by pushing the carrier ball with knurled outside
- The carrier balls can be fitted with **BPPL/TOOL** mounting tools.

### Application

- Transport, conveyor, workstation and packaging systems.



Mounting tool

### DISCOUNTS

| Qty         | 1+   | 6+   | 20+  | 40+        | 60+ |
|-------------|------|------|------|------------|-----|
| Disc. Price | -10% | -15% | -20% | On request |     |

| Part number | Ball |      | H1 | H2  | H3   | H4  | ØA<br>(H7)<br>Hole | Load<br>capacity<br>(kg) | Weight<br>(g) | Price<br>each<br>1 to 5 |         |
|-------------|------|------|----|-----|------|-----|--------------------|--------------------------|---------------|-------------------------|---------|
|             | ØD   | ØD1  |    |     |      |     |                    |                          |               |                         | ØD2     |
| BPPL6-10    | 6,5  | 10,0 | 13 | 3,2 | 11,2 | 1,2 | 4,2                | 10,0                     | 116           | 4                       | 13,69 € |
| BPPL8-12    | 8,5  | 12,6 | 17 | 4,5 | 12,4 | 1,8 | 4,2                | 12,6                     | 198           | 8                       | 14,87 € |

### Mounting tool

|               |  |                           |  |  |  |  |  |  |     |  |         |
|---------------|--|---------------------------|--|--|--|--|--|--|-----|--|---------|
| BPPL6-10/TOOL |  | For carrier ball BPPL6-10 |  |  |  |  |  |  | 118 |  | 29,82 € |
| BPPL8-12/TOOL |  | For carrier ball BPPL8-12 |  |  |  |  |  |  | 125 |  | 29,82 € |

Dimensions in mm

# Load carrying ball transfer units

## Technical information

|            | Max load (kg) | % load friction | Speed (m/sec) | Load shocks | Difficult conditions | Orientation | Omnidirectional |
|------------|---------------|-----------------|---------------|-------------|----------------------|-------------|-----------------|
| Range BPHR | 335           | 2               | 1,5           | ✓✓✓✓✓       |                      |             | ✓✓✓             |
| Range BPH  | 600           | 2               | 1,5           | ✓✓✓✓        | Options 'SS'         |             | ✓✓✓             |
| Range BPL  | 600           | 3               | 1             | ✓✓✓         | Options 'SS'         |             | ✓✓✓             |
| Range BPPE | 20            | 3               | 1             | ✓           |                      |             | ✓✓✓             |

### Load

The weight of the article to be moved should be divided by 3, this gives the maximum weight that any single ball will carry. If a greater positioning accuracy is required then this coefficient of 3 can be increased. The condition and surface hardness of the article to be moved should also be taken into account to avoid being marked by the balls.


$$\text{Load C} > \frac{\text{load weight}}{3}$$

### Spacing of ball transfer units


The pitch of the ball transfer units is determined by dividing the shortest dimension of the article to be moved by 3.5. This ensures that at least 3 ball transfer units will be in contact with article along its shortest dimension at any time.

$$\text{Spacing} = \frac{\text{shortest dimension}}{3,5}$$


#### Direction of movements



square pitch



Diamond



Elongated pitch spacing