

Pin for magnetic bush

BDM Fast and light magnetic locking

- Pin for magnetic bush

- Fastening element used to hold panels or thin plates. The pin is held in the bush housing by a magnet.
- Materials:
Natural finish steel


Info

- The pin is attracted to the magnetic bush **BDM6-7/DLL**.
- Mounting option with nut (not included) or by screwing directly into the workpiece.





Accessory


- Mounting pin **BDM6-7/DLL**



Typical application:
Quick assembly or removal of valves



Recommended mounting tolerances:



DISCOUNTS

Qty	1+	4+	8+
Disc. Price	-5%	On request	On request

Part N°	Shear force (kN)	Price per unit
BDM6-7	0.9	1 to 3 3,14 €

*Depending on availability - Dimensions in mm

Pin for magnetic bush

Fast and light magnetic locking **BDM6-7**

- Magnetic bush

- The pin BDM6-7 is held in the bush housing by a magnet which holds it with the specified clamping force.

- Materials:

Body in stainless steel natural finish
Neodymium magnet

- Working temperature range: max 80°C

Assembly







- Form A: min. plate thickness 6 mm.
- Form B: max. plate thickness 10 mm.
- Form C: plate thickness > 10 mm.
- Form D: blind hole.

Info

- Repeatability +/-0.25mm

Accessory

- Pin for magnetic bush BDM6-7



DISCOUNTS

Qty	1+	4+	8+
Disc. Price		-5%	On request

Part N°	Clamping force (N)	Shearing force (kN)	H1	SW	Price per unit 1 to 3
BDM6-7/DLL	7	0.8	-	-	12,60 €
DLL-M12-EC/SS	Nut for BDM6-7/DLL		6	19	0,57 €
DLL-M16-TOOL	Assembly tools for BDM6-7/DLL				20,81 €

*Depending on availability - Dimensions in mm

Our other products



H0

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



NK17

Drylin®N miniature
guiding system, Width
17 mm



BLHB60_

Right angled gearbox,
bored shafts, up to 70
Nm



PRF_ART

Articulated bracket for
use with aluminium
profile, Standard



UTKswrr

V shaped channel
UtiliTrak®, V rail




PRF19_E

Bracket for aluminium
profile, PRF19 to
PRF45



DOG258

Motor-gearbox 12V
and 24V DC, from 12
to 15 Nm



M0

Worm and wheel set,
Machined plastic
(delrin)




AKD

Bellows coupling
Gerwah®, from 22 to
600Nm



WS20

Drylin® W rail, Rail



M0

Worm and wheel set,
Machined plastic
(delrin)



S20

Short housing for
open linear bearing,
Opened - slim

Complementary products



BDM

Pin for magnetic bush,
Fast and light
magnetic locking