

## With pressure pin

### BSMLOK BSMSSLOK BSMPLOK

- Screw for positioning and indexing
- Spring plunger with LONG-LOK anti-vibration treatment
- For locating and positioning
- Hexagonal socket
- Materials:
  - Body: blackened steel (class 5.8) or stainless steel (303)
  - Pin: hardened steel, hardened stainless steel or plastic
  - LONG-LOK nylon thread
- Finish:
  - Body: black oxide (steel) or polished (stainless steel)

Size	Screwing in torque (Nm)	Unscrewing torque (Nm)
M5	0.10	0.25
M6	0.25	0.45
M8	0.40	0.60
M10	0.70	0.80
M12	1.00	1.20
M16	4.20	4.30




### Advantages

- Vibration proof
- High torque required to unscrew
- Mounts securely in any orientation

### Application

- Use where plungers are repeatedly installed and removed



### DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc.	List	-5%	-10%	-15%	-20%	-25%	On request

Part number	ØD	ØD1	L	L <sup>†0.5</sup>	H	T	T1	N	S	Pressure (N)		Stock*	Price each 1 to 5
										F1 initial	F2 final		
<b>Steel body / steel pin</b>													
BSM5/LOK	M5	2,4	18	7	2,3	2,0	0,8	0,8	1,5	6	20	✓	3,49 €
BSM6/LOK	M6	2,7	20	7	2,5	2,5	1,0	1,0	2,0	7	20	✓	3,59 €
BSM8/LOK	M8	3,5	22	8	3,0	3,0	1,4	1,2	2,5	9	35	✓	4,17 €
BSM10/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	9	35	✓	4,55 €
BSM12/LOK	M12	6,0	28	10	4,0	5,0	2,0	2,0	4,0	10	55	✓	7,37 €
BSM16/LOK	M16	7,5	32	14	5,0	6,0	2,5	2,5	5,0	45	100	-	10,28 €
<b>Stainless steel body / stainless steel pin</b>													
BSM5SS/LOK	M5	2,4	18	7	2,3	2,0	0,8	0,8	1,5	5	17	✓	7,89 €
BSM6SS/LOK	M6	2,7	20	7	2,5	2,5	1,0	1,0	2,0	6	17	✓	7,89 €
BSM8SS/LOK	M8	3,5	22	8	3,0	3,0	1,4	1,2	2,5	7	29	✓	8,84 €
BSM10SS/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	8	31	✓	10,22 €
BSM12SS/LOK	M12	6,0	28	10	4,0	5,0	2,0	2,0	4,0	10	47	✓	14,81 €
<b>Steel body / plastic pin</b>													
BSM5P/LOK	M5	2,4	18	7	2,3	2,0	0,6	0,8	1,5	6	20	✓	3,86 €
BSM6P/LOK	M6	2,7	20	7	2,5	2,5	0,8	1,0	2,0	7	20	✓	4,06 €
BSM8P/LOK	M8	3,5	22	8	3,0	3,0	1,0	1,2	2,5	9	35	✓	4,63 €
BSM10P/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	9	35	✓	5,33 €
BSM12P/LOK	M12	6,0	28	10	4,0	5,0	1,4	2,0	4,0	10	55	✓	8,26 €
BSM16P/LOK	M16	7,5	32	14	5,0	6,0	2,0	2,5	5,0	45	100	-	18,66 €

\*Subject to availability - Dimensions in mm

## Our other products



HTD5M\_09  
HTD Heavy duty timing pulley, HTD5 Steel



SH2  
Parallel axis helical gear, Machined plastic (delrin)



VDSCB  
Sliding lock adjustment system, Blocking wedge for sliding lock for ...



S\_2RS  
Deep groove ball bearing, Stainless steel



PLM-C  
Cylindrical holding magnets, Cylindrical holding magnet



YG3  
HEAVY DUTY spur gear, Steel 35NCD6



CHAB  
Hinge with stop, Hinge



BZY\_SS  
Stainless steel cylindrical elasto mount, Stainless steel



RESC  
Retractable castor for aluminium profile, Retractable castor



T10courroie  
T type timing belt, T10 Steel cored polyurethane



PTMR  
Telescopic furniture foot, threaded stud



DIL  
Lever operated locking bolt, lever clamp

## Complementary products



BSM\_LOK  
Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



BSM  
Spring plunger with internal hexagonal socket, steel body, plastic pin



BSM  
Spring plunger with internal hexagonal socket, steel body and pin



BSM\_LOK  
Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...