

With pressure pin

BSMLOK
BSMSSLOK
BSMPLOK

- Screw for positioning and indexing
- Spring plunger with LONG-LOK anti-vibration treatment
- For locating and positioning
- Hexagonal socket
- Materials:
 - Body: blackened steel (class 5.8) or stainless steel (303)
 - Pin: hardened steel, hardened stainless steel or plastic
 - LONG-LOK nylon thread
- Finish:
 - Body: black oxide (steel) or polished (stainless steel)

Size	Screwing in torque (Nm)	Unscrewing torque (Nm)
M5	0.10	0.25
M6	0.25	0.45
M8	0.40	0.60
M10	0.70	0.80
M12	1.00	1.20
M16	4.20	4.30




Advantages

- Vibration proof
- High torque required to unscrew
- Mounts securely in any orientation

Application

- Use where plungers are repeatedly installed and removed



DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc.	List	-5%	-10%	-15%	-20%	-25%	On request

Part number	ØD	ØD1	L	L ^{†0.5}	H	T	T1	N	S	Pressure (N)		Stock*	Price each 1 to 5
										F1 initial	F2 final		
Steel body / steel pin													
BSM5/LOK	M5	2,4	18	7	2,3	2,0	0,8	0,8	1,5	6	20	✓	3,49 €
BSM6/LOK	M6	2,7	20	7	2,5	2,5	1,0	1,0	2,0	7	20	✓	3,59 €
BSM8/LOK	M8	3,5	22	8	3,0	3,0	1,4	1,2	2,5	9	35	✓	4,17 €
BSM10/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	9	35	✓	4,55 €
BSM12/LOK	M12	6,0	28	10	4,0	5,0	2,0	2,0	4,0	10	55	✓	7,37 €
BSM16/LOK	M16	7,5	32	14	5,0	6,0	2,5	2,5	5,0	45	100	-	10,28 €
Stainless steel body / stainless steel pin													
BSM5SS/LOK	M5	2,4	18	7	2,3	2,0	0,8	0,8	1,5	5	17	✓	7,89 €
BSM6SS/LOK	M6	2,7	20	7	2,5	2,5	1,0	1,0	2,0	6	17	✓	7,89 €
BSM8SS/LOK	M8	3,5	22	8	3,0	3,0	1,4	1,2	2,5	7	29	✓	8,84 €
BSM10SS/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	8	31	✓	10,22 €
BSM12SS/LOK	M12	6,0	28	10	4,0	5,0	2,0	2,0	4,0	10	47	✓	14,81 €
Steel body / plastic pin													
BSM5P/LOK	M5	2,4	18	7	2,3	2,0	0,6	0,8	1,5	6	20	✓	3,86 €
BSM6P/LOK	M6	2,7	20	7	2,5	2,5	0,8	1,0	2,0	7	20	✓	4,06 €
BSM8P/LOK	M8	3,5	22	8	3,0	3,0	1,0	1,2	2,5	9	35	✓	4,63 €
BSM10P/LOK	M10	4,0	22	9	3,0	3,5	1,4	1,6	3,0	9	35	✓	5,33 €
BSM12P/LOK	M12	6,0	28	10	4,0	5,0	1,4	2,0	4,0	10	55	✓	8,26 €
BSM16P/LOK	M16	7,5	32	14	5,0	6,0	2,0	2,5	5,0	45	100	-	18,66 €

*Subject to availability - Dimensions in mm

Our other products



HW_HT
Half-rail guide, Wheel



PF40
Worm and wheel gear reducer, up to 18 Nm



B3PAN
Panamech, Multi-Beam stainless steel, Stainless steel - with clampin...



PRES7HR
Manual workbench press, Force up to 700kg



DOMI50
Accessories, Fixing kit



PAV
Fixed anti-vibration foot mount, Vibration-dampening



PITAss
Locking bolt, with T handle



MDR_SS
Stainless steel Dee shackle with eye bolt, Stainless steel



PRF4532
Standard aluminium profile, 45 x 32 mm



UCP_SS
Stainless steel pillow block bearing,



TPEpbd
Castor for aluminium profile, Swivel with



LF
Precision locknut, Precision locknut

Complementary products



BSM_LOK
Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



BSM
Spring plunger with internal hexagonal socket, steel body and pin



BSM
Spring plunger with internal hexagonal socket, steel body, plastic pin



BSM
Spring plunger with internal hexagonal socket, stainless steel 303 b...