

- Ideal for moving bottles and metal cans at high speeds

- Smooth surface with no backlash

- Non knurled pin

- Materials:


Plates: low friction acetal

Pin: stainless steel 304

- Operating temp.: -40°C to +85°C

(+70°C in humid environments)

- Length 3048mm (80 plates)



Advantages



- In most applications no lubrication is necessary

Associated products


- Drive sprocket **PT820**

- Idler sprocket **PR820**

- Idler **DBL820**



Direction of travel →



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP820-82	82,5	3048	3200	0,83	86,81 €
CAP820-114	114,3	3048	3200	1,03	110,57 €

Dimensions in mm

Our other products



DCA

Suction cup, 1.5 bellows, silicon



PARF80

Pressed steel base rigid foot, Swivelling - Ø80



CHT

Asynchronous AC Motor 1.1 to 1.85kW, 1.1 to 1.85kW



PNA

PERIFLEX® elastic coupling, Complete coupling



AC144

Strike for toggle latch, 22mm



SNG

Stainless/Polymer pillow block bearing, Cast iron - Split pillow



SUPTOOL

Installation tools for clamping hub, For hexagonal clamping hub



AC

Strike for toggle latch, 15mm



PRF4545

Standard stainless steel profile, 45 x 45



PLA

Flat magnet, Flat magnet with thread



PW_PWG3

Worm - precision range, Stainless steel



PR125

Articulated foot Ø123, Ø 123

Complementary products



PT820

Drive sprocket for slat top chain, Ranges 820 and 815



PR820

Idler sprocket for slat top chain, Ranges 820 and 815



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815