

- Ideal for moving bottles and metal cans at high speeds

- Smooth surface with no backlash

- Non knurled pin

- Materials:


Plates: low friction acetal

Pin: stainless steel 304

- Operating temp.: -40°C to +85°C

(+70°C in humid environments)

- Length 3048mm (80 plates)



Advantages



- In most applications no lubrication is necessary

Associated products


- Drive sprocket **PT820**

- Idler sprocket **PR820**

- Idler **DBL820**



Direction of travel →



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP820-82	82,5	3048	3200	0,83	86,81 €
CAP820-114	114,3	3048	3200	1,03	110,57 €


Dimensions in mm

Our other products




METEB

Self-lubricating blanks, Bronze BP25



INO

Internal gear, Machined plastic (delrin)



CRM

Moulded nylon rack, Nylon



OPFL_OPPM

Numerical counter accessories, Operating knob



ZAmm

Shaft for linear guides, Hardened ground steel



CHM110

Worm and wheel gear reducer, up to 980 Nm



SSG1_304L

Stainless steel spur gear, Stainless steel 304L



HRV

V-rail guidance Simple Select® system, Rail with carriage



JSM

Cylindrical polymer bush, Universal polymer



TBE12

Economic mini-table with trapezoidal leadscrew, 2kg



ADL_F

Female eye bolt conforms to DIN582, Steel



PPF

Indexing plunger with flange, with drilled flange

Complementary products



PT820

Drive sprocket for slat top chain, Ranges 820 and 815



PR820

Idler sprocket for slat top chain, Ranges 820 and 815



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815