Right angled gearbox, dual output shafts


Torque up to 128Nm


BLHM70

- ***Input and two outputs have a reversed sens of direction***
- *Ratios of 1:1 to 2:1*
- *Output backlash ≃1°*
- *Max. speed: 4,000 rpm*
- *Materials: casing: anodised aluminium*
  input: hardened steel,
  output: hardened steel
- *Weight: 8.76 kg*

Options

- *Can be modified to your specifications*





Output torque Nm (Nm values given as a guide only)

Ratios	1:1	2:1
3000	43	26
2000	47	30
INPUT 1000	51	34
SPEED 500	64	38
(rpm) 100	85	51
50	94	60
10	128	77

Innovative ! Outputs rotate in different directions

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ratio	Efficiency at 1000 rpm	Max. input speed (rpm)	Max. output speed (rpm)	Module	Price each
BLHM70-1	1:1	88%	3000	3000	4,0	On request
BLHM70-2	2:1	88%	3000	1500	2,5	On request

Dimensions in mm

Our other products



UTKpwc

Utilitrak® 3 wheels carriage, Polymer series V wheels



IN1

Internal gear, Steel 20NCD2



SMLS

Linear table, For small lengths



CHAR5050_Z

Spring hinge, screwed



MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



RPP8

RPP heavy duty timing belt, RPP8



DOG258

Motor-gearbox 12V and 24V DC, from 12 to 15 Nm




PAT123

Pressed stainless steel articulating foot Ø123, Ø 123




BPLF

Ball transfer unit light duty, Light



BLHM20

Right angled gearbox, double output shafts, up to 1.77 Nm



PF30NM

Worm and wheel gear reducer, up to 8.8 Nm



BSCm

Knurled torque knobs - male, Knurled threaded torque

Complementary products



BLH70

Right angled gearbox, from 26 to 128 Nm



BLHT70

Right angled gearbox, from 26 to128 Nm