


- Axle mounted eccentric cam follower
- Synthetic rubber joints fitted to external ring
- Assemble using a screwdriver
- Diameter of housing 6 to 18mm, tolerance H7
- Material: carbon steel



### Info.

- All the followers come with grease nipples: at the end of the axle on the roller side, on the threaded side, and on the cylindrical section,  
(Except for cam < 10 mm with only one hole on the roller side).



### DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Min. flange Ø f (mm)		Torque (Nm)	C (N)	Max. admissible load (N)	Max. speed (rpm)	Øg1 (mm)	g2 (mm)	r mini. (mm)	Eccentricity ε (mm)
	Basic static load C (N)	Basic dynamic load								
CFES6UUR	11	12.7	3660	3650	1980	-	-	0.3	0.25	
CFES8UUR	13	6.5	4250	4740	4670	-	-	0.3	0.25	
CFES10UUR	16	13.8	5430	6890	6890	-	-	0.3	0.30	
CFES10-1UUR	16	13.8	5430	6890	6890	-	-	0.3	0.30	
CFES12UUR	21	21.9	7910	9790	9790	4	3	0.6	0.40	
CFES12-1UUR	21	21.9	7910	9790	9790	4	3	0.6	0.40	
CFES16UUR	26	58.5	12000	18300	18300	4	3	0.6	0.50	
CFES18UU	29	86.2	14800	25200	25200	6	3	1.0	0.60	

Part number	d1 (h7)	D (h5)	C <sup>+0, -0.12</sup>	G	G1	B	B1	B2	B3	C1	Stock*	Price each 1 to 5
CFES8UUR	8	19	11	M8 x 1,25	10	12,2	32,2	20,0	-	0,6	✓	37,82 €
CFES10UUR	10	22	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	41,76 €
CFES10-1UUR	10	26	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	44,12 €
CFES12UUR	12	30	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	47,12 €
CFES12-1UUR	12	32	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	41,70 €
CFES16UUR	16	35	18	M16 x 1,50	17	19,6	52,1	32,5	8	0,8	-	56,70 €
CFES18UU	18	40	20	M18 x 1,50	19	21,6	58,1	36,5	8	0,8	✓	67,32 €

\*Depending on availability - Dimensions in mm

## Our other products



PFM  
Fixed levelling foot,  
Flanged plate



T10-BAR  
T type tooth bar  
stock, T10



M0  
Worm and wheel set,  
Machined plastic  
(delrin)




CQA20  
Adjustment slide-  
system miniature, 20



SEH  
Horizontal stirrup  
toggle clamp,  
Horizontal Latch  
clamp - stainless ...



G-ECO  
Eco range Spur gear,  
Steel C45



B  
Steel bevel gear, 1:1



BCA  
Steel splined collar,  
Steel



MHX  
Hexagonal threaded  
sleeve, Hexagonal -  
steel



GDR880  
Straight track for slat  
top chain, Ranges 880  
and 881



HLC19  
Right angle spiro  
bevel gearbox, Up to  
43Nm



GE32  
Sprung toggle latch  
with connecting link,  
Standard

## Complementary products



CFUURSS  
Cam follower stainless  
steel, Standard -  
stainless steel