

# High profile ball transfer unit


## BPLF

## For light loads

- **Pressed steel ball transfer unit with mounting plate**
- With 2 or 4 mounting holes for screws or rivets.  
(The BPLF25-55-2F has 2 slots rather than 2 holes to accommodate different centre distances)
- For light loads
- Housing made from pressed steel
- With drainage hole and felt seal.
- Orientation: horizontal with ball upwards
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:



**BPL:**galvanised steel body and steel balls  
**BPL/SS:**stainless steel body and stainless steel  
 420 balls



### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc. Prix	-10%	-15%	-20%	On request	

Part N°	Ødw ball	ØA	B	C	D	E	F	Carrying capacity (kg)	Weight (kg)	Stock*	Price each 1 to 5
<b>Steel body, steel balls</b>											
BPLF25-45-2F	25,4	45,0	30,4	6,3	69 x 51	55,9 - 60,3	Fente 2 x 5,5 x 7,7	55	0,155	✓	5,84 €
BPLF38-67-4	38,1	66,9	46,2	9,8	76,2 x 76,2	62,7 x 62,7	4 x Ø7,1	115	0,520	-	17,65 €
<b>Stainless steel body / Stainless steel ball</b>											
BPLF25-45-2F/SS	25,4	45,0	30,4	6,3	69 x 51	55,9 - 60,3	Fente 2 x 5,5 x 7,7	55	0,151	✓	15,21 €

\*Depending on availability - Dimensions in mm

## Our other products



SVR20

Screwjack with travelling nut, with moving nut



PSG25

Spur gear - precision range, Stainless steel 316



PML

Solid foot mount for heavy loads, Ø 100, 120 or 150



DCG

Suction cup, 2.5 bellows, silicon



VPSS

Small 6 lobe threaded handle - male, Duroplast - Stainless steel



GARQT

Quarter turn lock pin for clamping, Quarter turn



BC3

Panamech, Multi-Beam stainless steel, Stainless steel - with clampin...



GAC

Latch clamp with lock, Lockable



T10\_30\_AL

T type timing pulley, Economy range - T10 aluminium



BLHM50

Right angled gearbox, double output shafts, up to 30 Nm



PRF\_GAL

Roller for aluminium profile, Fixing kit for roller concentric



BSM\_LOK

Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...

## Complementary products



BPL

Ball transfer unit light duty, Light



BPLE

Ball transfer unit push fit, Light



BPLF

Ball transfer unit light duty, Light