

Stainless steel slotted spring plunger

BPMc

With ceramic ball tip

- **Positioning and locating screw**

- **Materials:**

Body: Stainless steel 303, natural finish

Spring: Stainless steel


Ball: Ceramic (Si3N4)

stainless steel



Info


- Use of a Si3N4 ceramic offers high resistance and grip, is hard wearing and is chemically resistant.



$$\alpha = 60^\circ, F1 = 1,732xF$$

$$\alpha = 90^\circ, F1 = F$$

$$\alpha = 120^\circ, F1 = 0,577xF$$



DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc. List		-5%	-10%	-15%	-30%	-50%	On request

Part number	ØD	ØD1	L	H	N	Pressure (N)		Weight (g)	Price each
						Initial F1	Final F2		
BPM5SS/C	M5	3	12	0,9	0,8	6	11	0,9	4,97 €
BPM6SS/C	M6	3,5	14	1	1	9	13	1,5	4,97 €
BPM8SS/C	M8	5	16	1,5	1,2	15	30	3,5	6,73 €
BPM10SS/C	M10	6	19	2	1,6	20	35	7	7,69 €
BPM12SS/C	M12	8	22	2,5	2	30	55	10	11,82 €
BPM16SS/C	M16	10	24	3,5	2,5	65	125	24	14,84 €

Dimensions in mm

Our other products



PT881

Drive sprocket for slat top chain, Range 881



CHA1056-U4

Screwed hinge, 180°



IN1

Internal gear, Steel 20NCD2



PV2R

Adjustable suction-cup support, Increased grip



ALIDRP240

24V DC power supply, 10 A



PTAF80-PAMF80

Articulated fixable foot with pressed base Ø80, Ø 80



AT5M AT10M

AT type timing belt per metre, AT10 Steel cored polyurethane



CHML50

Worm and wheel gear reducer, up to 107 Nm - Integrated torque limiter



PFC

Fixed rubber levelling foot, Levelling support for small parts



SSDB

Stainless steel bevel gear, 2:1



SLVVIok

Vertical toggle clamp, Vertical toggle clamp / vertical foot



VB

Small 6 lobe threaded handle - female, Duroplast - Stainless steel

Complementary products



BPM-Z

Plastic slotted spring plunger with ball tip, Plastic body + stainless steel



BPM

Slotted spring plunger with ball tip, Stainless steel 303



BPM_LOK

Long-Lok slotted spring plunger with ball tip, LONG-LOK - Steel



BPM_LOK

Long-Lok slotted spring plunger with ball tip, LONG-LOK - Stainless steel