

Flange mounting ball transfer unit


Plastic

BPPE

- **Plastic ball mounting ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- Clips compensate for irregularities in seat bore diameter
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:
Acetal body and balls (POM)

Advantages

- Resists salt water and chemical attacks
- Non-conductive and non-magnetic
- Suitable for antimicrobial applications
- For use in chemical, pharmaceutical and medical applications



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	C	ØD	E	Carrying capacity (kg)	Weight (g)	Price each 1 to 5
BPPE15-24/PP	15	24	8,0	4,8	30	20,0	7	0,010	18,29 €
BPPE22-36/PP	22	36	9,8	4,5	45	30,5	10	0,035	27,43 €
BPPE30-45/PP	30	45	13,8	5,8	55	37,0	15	0,065	32,65 €
BPPE45-62/PP	45	62	19,0	8,5	75	53,5	20	0,182	72,36 €

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

255

Our other products



BIM
Indexing plunger mini,
miniature



GGP
Male wing knob,
Technopolymer with
stainless steel spindle



DOMI30
Domino 30 adjustable
slide, Slide DOMILINE
30 with counter and
handw...



J53
Spur gear coaxial
gearbox, from 0.43 to
1.15 - In-line



NAST
Cam follower without
axial guide, With
interior ring



BLH30
Right angled gearbox,
from 1.32 to 4.40 Nm



G1
Steel spur gear, Steel
20NCD2



HRV
V-rail guidance
Simple Select®
system, Rail with
carriage




SH0
Parallel axis helical
gear, Steel 20NCD2



PDR-RD
Mounting feet with
integrated castors,



CMAss
Eye bolt stainless
steel, Stainless steel



MEP
Revolving handle for
handwheel, Fixed

Complementary products



BPHFclip
Clip for ball transfer
unit, Insert clip -
Installing from above



BPLe
Ball transfer unit push
fit, Light



BPHF
Ball transfer unit push
fit, Heavy



BPHF
Ball transfer unit push
fit, Heavy