

# Flange mounting ball transfer unit


Plastic

BPPE

- **Plastic ball mounting ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- Clips compensate for irregularities in seat bore diameter
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:  
Acetal body and balls (POM)

## Advantages

- Resists salt water and chemical attacks
- Non-conductive and non-magnetic
- Suitable for antimicrobial applications
- For use in chemical, pharmaceutical and medical applications



## DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	C	ØD	E	Carrying capacity (kg)	Weight (g)	Price each 1 to 5
BPPE15-24/PP	15	24	8,0	4,8	30	20,0	7	0,010	18,29 €
BPPE22-36/PP	22	36	9,8	4,5	45	30,5	10	0,035	27,43 €
BPPE30-45/PP	30	45	13,8	5,8	55	37,0	15	0,065	32,65 €
BPPE45-62/PP	45	62	19,0	8,5	75	53,5	20	0,182	72,36 €

All dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

Fax

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

255

## Our other products



DOMI120

Accessories, Clamping lever



HK

Manual locking clamp,  
Manual locking clamp  
T



R\_RR

Narrow spur rack,  
Steel



HG5

Steel spur gear, Steel  
20NCD2



DOMI30

Accessories, Turntable



RJA00\_28

Sealing strip, Clipping



HLUMss

Revolving handle for  
handwheel, Stainless  
steel 316




CHAsb89

Hinge without pin,  
Plastic hinge



CPAS

Stay with safety  
catch, Opens upward



PRF4545r90

Standard aluminium  
profile, 45 x 45 mm -



HSE-HSB

Hexagonal spacer,  
Steel



BPH

Ball transfer unit plain  
fit, High

## Complementary products



BPHFclip

Clip for ball transfer  
unit, Insert clip -  
Installing from above



BPLE

Ball transfer unit push  
fit, Light



BPHF

Ball transfer unit push  
fit, Heavy



BPHF

Ball transfer unit push  
fit, Heavy