

# Spring plunger with internal hexagonal socket

With pressure pin

**BSM**  
**BSMP**  
**BSMss**

- Three versions to choose from

- Materials:

Body: blackened steel (class 5.8) or stainless steel (303)

Pin: steel, stainless steel or plastic



Steel body and pin




Steel body plastic pin



Stainless steel body and pin

## Uses

- Locating
- Retaining



## DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc.	List	-5%	-10%	-15%	-30%	-50%	On request

Part number	ØD	ØD1	L	H	T	T1	N	S	Pressure (N)		Price each 1 to 5	
									F1 initial	F2 final		
<b>Steel body / steel pin</b>												
BSM3	M3	1,0	10	1,5	1,5	1,0	0,4	0,7	0,5	3	✓	9,01 €
BSM4	M4	1,5	15	1,5	2,0	0,6	0,6	1,3	5	16	✓	6,91 €
BSM5	M5	2,4	18	2,3	2,0	0,8	0,8	1,5	6	20	✓	6,73 €
BSM6	M6	2,7	20	2,5	2,5	1,0	1,0	2,0	7	20	✓	6,97 €
BSM8	M8	3,5	22	3,0	3,0	1,4	1,2	2,5	9	35	✓	8,22 €
BSM10	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	9	35	✓	9,20 €
BSM12	M12	6,0	28	4,0	5,0	2,0	2,0	4,0	10	55	✓	12,02 €
BSM16	M16	7,5	32	5,0	6,0	2,5	2,5	5,0	45	100	✓	13,27 €
BSM20	M20	10,0	40	7,0	8,0	3,0	2,5	6,0	60	120	✓	15,70 €
BSM24	M24	12,0	52	10,0	10,0	3,0	2,5	8,0	80	160	-	25,28 €
<b>Steel body / plastic pin</b>												
BSM4P	M4	1,5	15	1,5	2,0	1,0	0,6	1,3	5	16	✓	8,03 €
BSM5P	M5	2,4	18	2,3	2,0	0,6	0,8	1,5	6	20	✓	7,83 €
BSM6P	M6	2,7	20	2,5	2,5	0,8	1,0	2,0	7	20	✓	8,03 €
BSM8P	M8	3,5	22	3,0	3,0	1,0	1,2	2,5	9	35	✓	9,36 €
BSM10P	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	9	35	-	11,20 €
BSM12P	M12	6,0	28	4,0	5,0	1,4	2,0	4,0	10	55	-	14,15 €
BSM16P	M16	7,5	32	5,0	6,0	2,0	2,5	5,0	45	100	-	17,30 €
<b>Stainless steel body / stainless steel pin</b>												
BSM5SS	M5	2,4	18	2,3	2,0	0,8	0,8	1,5	5	17	✓	19,83 €
BSM6SS	M6	2,7	20	2,5	2,5	1,0	1,0	2,0	6	17	✓	19,78 €
BSM8SS	M8	3,5	22	3,0	3,0	1,4	1,2	2,5	7	29	✓	22,03 €
BSM10SS	M10	4,0	22	3,0	3,5	1,4	1,6	3,0	8	31	✓	30,06 €
BSM12SS	M12	6,0	28	4,0	5,0	2,0	2,0	4,0	10	47	✓	40,70 €

\*Depending on availability - Dimensions in mm

## Our other products



Brush strip per meter horsehair fibres Ø0.2, Black horsehair



Clip for bonnet fastener, Clip



Mechanical catch, Quick closing catch



Pad eye on mounting plate oval, Stainless steel



Internal epicyclic servo reducers, from 210 to 380 Nm



Variable angle connector, Variable angle



Spoked handwheel without handle, Aluminium




Cable clip for aluminium profile, For cable chute



Mounting bracket for bonnet fastener, Hook



Rounded end feather key, Steel



Screen support, Basic support



Extension springs DIN2097, DIN 2097

## Complementary products



Spring plunger with internal hexagonal socket, steel body and pin



Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



Spring plunger with internal hexagonal socket, steel body, plastic pin