

Spring loaded position switch

Limit switch feedback


CFC

- **Threaded position switch**
- Inductive limit switch for position sensing
- Electrical characteristics:
 - Supply voltage 10 to 30V dc
 - Max switching current 200mA
 - Working temperature: -25°C to +70°C
 - Ingress protection: IP67
 - Connecting cable: Ø3.5mm, length 2m
- Materials:
 - Body: blackened steel
 - Spring: steel
 - Pin: Hardened steel





Safety

- This position switch is not suitable for use in personnel safety applications



Wiring diagram



Typical application

DISCOUNTS

Qty	1+	6+	20+
Disc. List	-5%	On request	

Part number	ØD	ØD1	L	H	H1	L1	Contact pressure (N) initial	final	Stock*	Price each 1 to 5
Type O - contact normally open										
CFC-M6-O	M6	2,5	27,0	3	2	0,5	6	20	✓	63,08 €
CFC-M8-O	M8	4,0	28,5	3	2	0,7	15	30	✓	68,71 €
CFC-M10-O	M10	4,5	32,0	4	3	1,0	9	35	✓	72,18 €
Type F - contact normally closed										
CFC-M6-F	M6	2,5	3	3	2	1,2	6	20	✓	67,91 €
CFC-M8-F	M8	4,0	3	3	2	1,5	15	30	✓	68,71 €
CFC-M10-F	M10	4,5	4	4	3	2,0	9	35	✓	72,18 €

*Depending on availability - Dimensions in mm

Our other products



PR85

Articulated foot Ø83,
Ø 83



PTA100

Articulated levelling
foot, pressed base
Ø100, Ø 100



AT5P_AT10P

Connecting plate for
AT type timing belts,
AT10



J52

Spur gear coaxial
gearbox, from 0.27 to
0.90 Nm - In-line



RHTplss

High Temperature
Castor, up to 200kg



WSSss

Symmetrical S shaped
hook stainless steel,
Stainless steel



PRF_ROUL_F_

Castor for aluminium
profile, With brake



CHM40

Worm and wheel gear
reducer, up to 57 Nm



AF

Shaft clamp with
keyway, Set screw



HSE-HSB

Hexagonal spacer,
Brass



DER90


Stainless steel AC
asynchronous motor
1.1 - 1.5kW, 1.1 to
1.5kW



BOX-TOR-A

Box set of Nitrile O-
rings in nitrile, 2.90 x
1.78mm to 28.17 x
3.53

Complementary products



CFC

Spring loaded position
switch, Electric
contact