


- **Axle mounted eccentric cam follower**
- Synthetic rubber joints fitted to external ring
- Assemble using a screwdriver
- Diameter of housing 6 to 18mm, tolerance H7
- Material: carbon steel

Info.

- All the followers come with grease nipples: at the end of the axle on the roller side, on the threaded side, and on the cylindrical section,
(Except for cam < 10 mm with only one hole on the roller side).



Adjustable backlash



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Min. flange Ø f (mm)	Torque (Nm)	C (N)	Max. admissible load (N)	Max. speed (l) (rpm)	Øg1 (mm)	g2 (mm)	r mini. (mm)	Eccen- tricity ε (mm)
CFES6UUR	11	12.7	3660	3650	1980	-	-	0.3	0.25
CFES8UUR	13	6.5	4250	4740	4670	-	-	0.3	0.25
CFES10UUR	16	13.8	5430	6890	6890	-	-	0.3	0.30
CFES10-1UUR	16	13.8	5430	6890	6890	-	-	0.3	0.30
CFES12UUR	21	21.9	7910	9790	9790	4	3	0.6	0.40
CFES12-1UUR	21	21.9	7910	9790	9790	4	3	0.6	0.40
CFES16UUR	26	58.5	12000	18300	18300	4	3	0.6	0.50
CFES18UU	29	86.2	14800	25200	25200	6	3	1.0	0.60

Part number	d1 (h7)	D (h5)	C ^{+0.12}	G	G1	B	B1	B2	B3	C1	Stock*	Price each 1 to 5
CFES6UUR	6	16	11	M6 x 1.00	8	12.2	28.2	16.0	-	0.6	✓	36.38 €
CFES8UUR	8	19	11	M8 x 1.25	10	12.2	32.2	20.0	-	0.6	✓	37.82 €
CFES10UUR	10	22	12	M10 x 1.25	12	13.2	36.2	23.0	-	0.6	✓	41.76 €
CFES10-1UUR	10	26	12	M10 x 1.25	12	13.2	36.2	23.0	-	0.6	✓	44.12 €
CFES12UUR	12	30	14	M12 x 1.50	13	15.2	40.2	25.0	6	0.6	-	47.12 €
CFES12-1UUR	12	32	14	M12 x 1.50	13	15.2	40.2	25.0	6	0.6	-	41.70 €
CFES16UUR	16	35	18	M16 x 1.50	17	19.6	52.1	32.5	8	0.8	-	56.70 €
CFES18UU	18	40	20	M18 x 1.50	19	21.6	58.1	36.5	8	0.8	✓	67.32 €

*Depending on availability - Dimensions in mm

Our other products



Indexing plunger with flange, With horizontal mounting flange



Weld-on hinge with flat end, Stainless steel or Aluminium



Crossed helical gear crossed axis at 90°, Steel 20NCD2



Worm and wheel gear reducer, up to 107 Nm - Integrated torque limiter



Self-centering clamping hub stainless steel, With lock nut



Parallel axis helical gear, Steel 20NCD2



Articulated levelling foot, pressed base Ø50, 4000N



Plain washer, A2 Stainless steel



Motor-gearbox 12V and 24V DC, from 1.5 to 6 Nm



Lock for aluminium profile, Quick fitting, self locking door lock



Asynchronous AC Motor, 0.55 to 1.1kW



Hexagonal headed screw with collar Hygienic Usit®, Stainless steel

Complementary products



Cam follower stainless steel, Standard - stainless steel