


- Axle mounted eccentric cam follower
- Synthetic rubber joints fitted to external ring
- Assemble using a screwdriver
- Diameter of housing 6 to 18mm, tolerance H7
- Material: carbon steel



Info.

- All the followers come with grease nipples: at the end of the axle on the roller side, on the threaded side, and on the cylindrical section,
(Except for cam < 10 mm with only one hole on the roller side).



DISCOUNTS


Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Min. flange Ø f (mm)		Torque (Nm)	C (N)	Max. admissible load (N)	Max. speed (rpm)	Øg1 (mm)	g2 (mm)	r (mm)	Eccentricity ε (mm)
	Max. locking	Basic dynamic load	Basic static load C (N)	Max. load C (N)						
CFES6UUR	11	12,7	3660	3650	1980	-	-	0,3	0,25	
CFES8UUR	13	6,5	4250	4740	4670	-	-	0,3	0,25	
CFES10UUR	16	13,8	5430	6890	6890	-	-	0,3	0,30	
CFES10-1UUR	16	13,8	5430	6890	6890	-	-	0,3	0,30	
CFES12UUR	21	21,9	7910	9790	9790	4	3	0,6	0,40	
CFES12-1UUR	21	21,9	7910	9790	9790	4	3	0,6	0,40	
CFES16UUR	26	58,5	12000	18300	18300	4	3	0,6	0,50	
CFES18UU	29	86,2	14800	25200	25200	6	3	1,0	0,60	

Part number	d1 (h7)	D (h5)	C ^{+0, -0,12}	G	G1	B	B1	B2	B3	C1	Stock*	Price each
												1 to 5
CFES6UUR	6	16	11	M6 x 1,00	8	12,2	28,2	16,0	-	0,6	✓	36,38 €
CFES8UUR	8	19	11	M8 x 1,25	10	12,2	32,2	20,0	-	0,6	✓	37,82 €
CFES10UUR	10	22	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	41,76 €
CFES10-1UUR	10	26	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	44,12 €
CFES12UUR	12	30	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	47,12 €
CFES12-1UUR	12	32	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	41,70 €
CFES16UUR	16	35	18	M16 x 1,50	17	19,6	52,1	32,5	8	0,8	-	56,70 €
CFES18UU	18	40	20	M18 x 1,50	19	21,6	58,1	36,5	8	0,8	✓	67,32 €

*Depending on availability - Dimensions in mm

Our other products



KGS

Ballscrew, supplied by the metre, Rolled ballscrew, per metre



TM_CTM_CTF

Suction cup threaded insert, Insert for suction cup - Tread click-in



MBF

Threaded blocking clamp, Threaded locking clamp



PRES7HR

Manual workbench press, Force up to 700kg



AFA

Locking pin, with ring



CHMX_CHMDX

Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...



CHAK

Hi-Klik TM indent hinge, Hi-Klik™ - Detent hinge



T5M T10M

T type timing belt per metre, T10 Steel cored polyurethane



HTD14M_85

HTD Heavy duty timing pulley, HTD14 Cast



OP3_14_06

Reducing sleeve for OP indicators, Reduction socket



PO

Pull handle - Multi-sector, Smooth hole



PRF-SMA

Closing system for aluminium profile, Easily adjustable lock

Complementary products



CFUURSS

Cam follower stainless steel, Standard - stainless steel