


# Worm and wheel gearbox



## CHMR30


## Torque up to 28 Nm

- Ratios from 7.5:1 to 80:1
- Output backlash: N/A
- Max. input speed: 2,800 rpm
- Max. output speed: see CHMR30
- Materials:
  - Casing: aluminium
  - Screws: hardened steel
  - Wheel: bronze (cast iron hub)
- Lubrication: synthetic oil ISO VG320
- Weight: 1.2 kg



### Accessories

- Output shaft **CHM30-X** or **CHM30-DX**
- Torque arm **CHM30-BR**



### Output torque (Nm values given as a guide only)

Ratios	7.5:1	10:1	15:1	20:1	25:1	30:1	40:1	50:1	60:1	80:1	
INPUT SPEED (rpm)	2800	12	12	12	11	15	14	13	12	11	10
OUTPUT SPEED (rpm)	1400	17	17	17	17	20	19	17	16	15	12
OUTPUT TORQUE (Nm)	900	19	19	19	19	22	20	19	17	16	14
OUTPUT TORQUE (kgm)	500	23	23	23	22	28	25	22	20	18	16

### DISCOUNTS

Qty	1+	3+	6+
Disc.	List -20%	On request	On request

Part number	Reduction ratio	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 900 rpm (%)	Self locking output	Stock*	Price each 1 to 2
CHMR30-7	7.5:1	2800	373,33	NC	no	✓	132,58 €
CHMR30-10	10:1	2800	280,00	NC	no	✓	132,58 €
CHMR30-15	15:1	2800	186,66	NC	no	✓	132,58 €
CHMR30-20	20:1	2800	140,00	NC	no	-	132,58 €
CHMR30-25	25:1	2800	112,00	NC	no	✓	132,58 €
CHMR30-30	30:1	2800	93,33	NC	not defined	-	132,58 €
CHMR30-40	40:1	2800	70,00	NC	not defined	✓	132,58 €
CHMR30-50	50:1	2800	56,00	NC	not defined	✓	132,58 €
CHMR30-60	60:1	2800	46,66	NC	yes	✓	132,58 €
CHMR30-80	80:1	2800	35,00	NC	yes	✓	132,58 €

\*Depending on availability - Dimensions in mm

HPC

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



CHAR

Spring hinge, screwed



KB\_OP

Open precision linear bearing, Precision - steel



PPJ

Indexing plunger with flange, With horizontal mounting flange and pu...



PENC

Recessed handle, clip-in



SH0

Parallel axis helical gear, Steel 20NCD2



CLQ

12.7mm wide steel feeler strip on rolls, Feeler strip on rolls



CHA35

Hinge for aluminium profile, Hinge



SRP

Slotted spring pin ISO8752, Split ISO 8752



CHA\_GC\_14SS

Stainless steel garnet hinge, To screw



APB\_BOU

Protective cap, Safety cap



BUT

Panel stop, Panel stop



CHMR90

Worm and wheel gear reducer, up to 540 Nm

## Complementary products



CHMX\_CHMDX

Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...



CHMBR

Reaction arm, CHM and CHMR gear reducers reaction arm



P30

Worm and wheel gear reducer, up to 8.80 Nm