

CHARCAV

Very easy to install

- Spring-loaded hinges with stopper to lock the hinges in the open position for easy assembly

- 270° opening angle

- Material

304 stainless steel, stainless steel spring

- Spring torque

Opening spring:

M(0°): 1.6 Nm

M(90°): 1.2 Nm

M(180°): 0.84 Nm

Closing spring:





M(0°): 0.75 Nm

M(90°): 1.2 Nm

M(180°): 1.65 Nm

Info

- Spring hinge opens or closes delivered flat



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Type	Weight (g)	Stock*	Price each 1 to 5
CHAR8555/CAV	85	55	2	5	opening	107	-	23,33 €
CHAR8555-F/CAV	85	55	2	5	closing	107	-	23,33 €

*Depending on availability - Dimensions in mm

Our other products



ABL100005

Antistatic brush,
Standard



UGPL

Actuator guide kit,
Long bearing



RBGpl

Swivel castor with
double brake, Steel -
grey rubber



DB

Steel bevel gear, 2:1



BAGtr

Lead screw clamping
collar, Aluminium



BSM

Spring plunger with
internal hexagonal
socket, steel body and
pin



PGM52-M4

Pull handle,
Aluminium




NDS20

Double cross clamp,
Parallel



CQA20

Accessory for
adjustment slide-
system, 20



PM4

Worm and wheel set,
Machined plastic
(delrin)



PRF_ROUL_F

Castor for aluminium
profile, With brake



LRR-53

Spring loaded latch,
Spring return latch -
stainless steel

Complementary products



CHAR7530

Spring hinge, welded



CHAR6035

Spring hinge,
screwed/welded



CHAR7520

Spring hinge, screwed



CHAR16046

Spring hinge, screwed