

CHARCAV

Very easy to install

- Spring-loaded hinges with stopper to lock the hinges in the open position for easy assembly

- 270° opening angle

- Material

304 stainless steel, stainless steel spring

- Spring torque

Opening spring:

M(0°): 1.6 Nm

M(90°): 1.2 Nm

M(180°): 0.84 Nm

Closing spring:





M(0°): 0.75 Nm

M(90°): 1.2 Nm

M(180°): 1.65 Nm

Info

- Spring hinge opens or closes delivered flat



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Type	Weight (g)	Stock*	Price each 1 to 5
CHAR8555/CAV	85	55	2	5	opening	107	-	23,33 €
CHAR8555-F/CAV	85	55	2	5	closing	107	-	23,33 €

*Depending on availability - Dimensions in mm

Our other products



PLM-C

Flat gripping magnet,
Flat holding magnet



SSG2_304L

Stainless steel spur
gear, Stainless steel
304L



ZG4

Plastic spur gear,
Machined plastic
(delrin)



SRP

Slotted spring pin
ISO8752, Split ISO
8752




DILC

Indexing plunger with
cam, with cam




ADL_F

Female eye bolt
conforms to DIN582,
Steel



RPPM

RPP type belt per
metre, RPP8 Steel
cored polyurethane



ACLBTS

Closing system for
aluminium profile, 90°
bracket for spherical
end...



AFM

Flanged polymer
bush, Food grade
polymer



CLAT

Clamping lever
Hygienic Usit® -
male, Stainless steel



BABpss

301 Stainless steel
ball pin, Stainless
steel



M0

Worm and wheel set,
Machined plastic
(delrin)

Complementary products



CHAR7530

Spring hinge, welded



CHAR6035

Spring hinge,
screwed/welded



CHAR7520

Spring hinge, screwed



CHAR16046

Spring hinge, screwed