

Warning chain

CHN_{RB}

With long red and white links


- Steel chain supplied by the box
- Red and white painted steel

Applications

- Warning, signalling

Info

- Not to be used for lifting applications



DISCOUNTS

Qty	1+	3+	10+
Disc.	Net -10%		On request

Part number	Link ØT	P	E	Typical working load (kg)	Length per box	Weight per box (kg)	Price each 1 to 2
CHN-5/RB/B	5	35	10	155	25	10,50	123,13 €

All dimensions in mm

HPC

WEB
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



GG2

Ground spur gear,
Heat treated steel



UCFL

Cast iron flanged
bearing, Cast iron



ZDB

Machined plastic
bevel gear , 2:1



SEV

Vertical stirrup toggle
clamp, Vertical Latch
Clamp - steel



LVT

Miniature motorised
actuator 2A, 2 ampers



LVT

Miniature motorised
actuator 2A, 2 ampers



HSE-HSB

Hexagonal spacer,
Brass



PR880

Idler sprocket for slat
top chain, Range 880



PTCR

Adjustable furniture
foot, square tube



BZY_SS

Stainless steel
cylindrical elasto



DP

Dowel pin, Solid ISO
2338



PFM

Fixed levelling foot,
Flanged plate

Complementary products



CHN_CHNSS

Straight long link
chain, Galvanised
steel



MRA

Quick link, Steel



MAC

Carabiner DIN5299
steel, Steel



PPCss

Pad eye on mounting
plate squarred,
Stainless steel