

Warning chain

CHN_{RB}

With long red and white links


- Steel chain supplied by the box
- Red and white painted steel

Applications

- Warning, signalling

Info

- Not to be used for lifting applications



DISCOUNTS

Qty	1+	3+	10+
Disc.	Net -10%	Net -10%	On request

Part number	Link ØT	P	E	Typical working load (kg)	Length per box	Weight per box (kg)	Price each 1 to 2
CHN-5/RB/B	5	35	10	155	25	10,50	123,13 €

All dimensions in mm

HPC

WEB
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



RFVcap

Stainless steel
protective cover,
Open protective cover



PLM-20SC

Cylindrical magnet,
Cylindrical magnet



NDS20

Double cross clamp,
Crossed



UGH25

H Type Guide units,
For Ø25 actuators



TR

Spur round rack,
Stainless steel -
module 0,25-1,5



SBF

Sealed flange bearing
unit for Food Industry,
cover



BLHM70

Right angled gearbox,
up to 128 Nm




BLH70

Right angled gearbox,
from 26 to 128 Nm



GLB

Small 6 lobe threaded
handle - female,
Technopolymer -



KGS

Ball screw, supplied by
the metre, Rolled
ball screw, per metre



EFTC

Fixing support,
Stainless steel



BPM


Slotted spring plunger
with ball tip, Stainless
steel 303

Complementary products



CHN_CHNSS

Straight long link
chain, Galvanised
steel



MRA

Quick link, Steel



MAC

Carabiner DIN5299
steel, Steel



PPCss

Pad eye on mounting
plate squarred,
Stainless steel