

# 12.7mm wide steel feeler strip on rolls

## CLQ

## Steel or stainless steel

- Rolls of precision feeler strip for adjusting, straightening, positioning or levelling

- Width 12.7mm

- Length per roll: 5 metres

(\*except CLQ12-10-001 which is supplied on a 10 metre roll)

- Strip to be cut to form required

- Materials:

Steel 1.1274

Stainless steel 1.4310



steel or stainless steel

**NEW!**

### Applications

- Aligning workpieces before machining


- Aligning differently sized/shaped pieces

- Adjusting valve lash

- Wedging tools

- Adjusting bearings

- Aligning a motor and a pump before coupling



Incorrectly aligned



Wedge adjustment

### DISCOUNTS

|       |      |     |            |
|-------|------|-----|------------|
| Qty   | 1+   | 3+  | 5+         |
| Disc. | List | -5% | On request |

| Part number   |                 | Thickness (mm) | Price each 1 to 2 |         |
|---------------|-----------------|----------------|-------------------|---------|
| Steel         | Stainless steel |                | Steel             | S/Steel |
| CLQ12-10-001* | CLQ12-5-001/SS  | 0,01           | 93,68 €           | 51,24 € |
| CLQ12-5-002   | CLQ12-5-002/SS  | 0,02           | 39,32 €           | 34,57 € |
| CLQ12-5-003   | CLQ12-5-003/SS  | 0,03           | 15,97 €           | 17,87 € |
| CLQ12-5-004   | CLQ12-5-004/SS  | 0,04           | 15,00 €           | 15,26 € |
| CLQ12-5-005   | CLQ12-5-005/SS  | 0,05           | 14,31 €           | 12,87 € |
| CLQ12-5-006   | CLQ12-5-006/SS  | 0,06           | 11,44 €           | 12,87 € |
| CLQ12-5-007   | CLQ12-5-007/SS  | 0,07           | 10,72 €           | 12,87 € |
| CLQ12-5-008   | CLQ12-5-008/SS  | 0,08           | 10,25 €           | 12,87 € |
| CLQ12-5-010   | CLQ12-5-010/SS  | 0,10           | 9,77 €            | 11,68 € |
| CLQ12-5-015   | CLQ12-5-015/SS  | 0,15           | 10,25 €           | 13,35 € |
| CLQ12-5-020   | CLQ12-5-020/SS  | 0,20           | 10,50 €           | 14,06 € |
| CLQ12-5-025   | CLQ12-5-025/SS  | 0,25           | 10,96 €           | 15,50 € |
| CLQ12-5-030   | CLQ12-5-030/SS  | 0,30           | 10,72 €           | 16,10 € |
| CLQ12-5-040   | CLQ12-5-040/SS  | 0,40           | 12,16 €           | 20,73 € |
| CLQ12-5-050   | CLQ12-5-050/SS  | 0,50           | 11,91 €           | 22,16 € |

Dimensions in mm

## Our other products



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane



PSG1HC

Skive hobbled spur gears - precision range, Case hardened steel 20NCD2



MFBS

Stainless steel flexible bellows coupling, Stainless steel - with se...



CLG3

Moulded plastic spur gear, Moulded plastic (nylon)



BDP1R

Adjustable support arm, Single clamp



CHM50-MOT

Asynchronous AC motorgearboxes 0.18 to 0.75kW, 0.18 to 0.75kW



AWMP

Aluminium shaft for linear guide, Aluminium



PTA150

Articulated levelling foot, pressed base Ø150, Ø 150



G1

Steel spur gear, Steel 20NCD2



DILC

Indexing plunger with cam, with cam



PAMF80EB

Articulated foot with sheet metal base



GBS

Nut for ballscrew, Flanged ballscrew nut

## Complementary products



CLQassortiment

Assorted feeler strips, Assorted feeler strips