

# Clevis and clip, short version




CLSSs  
CLPSSs


With **stainless steel** circlips

- Trunnion link
- Material: stainless steel 303
- To DIN 71752, DIN 471-UNI7435
- Spring clip supplied with 2 circlips

Clevis CLS-SS



Clip CLP-SS



End fitting

stainless steel



Clip CLP-SS



CLS-SS



CLP-SS

## DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-10%	-20%	On request

Part number	Ød2 (6H)	b1 (B13)	a1 (h11)	a2	Ød1 (h9)	d3 <sup>+0,3</sup>	L1 <sup>+0,2</sup>	L3 <sup>+0,5</sup>	L2 <sup>+0,3</sup>	g <sup>+0,5</sup>	Static load Co (daN)	Stock*	Price each
												1 to 5	
CLS-5SS	M5	5	10	10 <sup>+0,30</sup> <sub>-0,16</sub>	5	9	7,5	26	20	10	500	✓	6,36 €
CLS-6SS	M6	6	12	12 <sup>+0,30</sup> <sub>-0,16</sub>	6	10	9,0	31	24	12	720	✓	6,82 €
CLS-8SS	M8	8	16	16 <sup>+0,30</sup> <sub>-0,16</sub>	8	14	12,0	42	32	16	1280	✓	11,47 €
CLS-10CSS	M10x1,25	10	20	20 <sup>+0,30</sup> <sub>-0,16</sub>	10	18	15,0	52	40	20	-	✓	26,47 €
CLS-12SS	M12x1,75	12	24	24 <sup>+0,30</sup> <sub>-0,16</sub>	12	20	18,0	62	48	24	2880	✓	34,49 €
CLS-16CSS	M16x1,5	16	32	32 <sup>+0,30</sup> <sub>-0,16</sub>	16	26	24,0	83	64	32	-	✓	81,44 €
CLS-20CSS	M20x1,5	20	40	40 <sup>+0,50</sup> <sub>-0,20</sub>	20	34	30,0	105	80	40	-	-	On request

## Trunnion clip

Références	Ød1 (h11)	d2	L <sup>+0,3</sup>	LH <sup>+0,3</sup>	m (H13)	e	Ød3	s	Circlip size (h11)	Stock*	Price each
										1 to 5	
CLP-5SS	5	4,8 <sup>0</sup> <sub>-0,048</sub>	15,0	10,5	0,7	0,5	4,7 <sup>+0,04</sup> <sub>-0,15</sub>	0,6	✓	2,23 €	
CLP-6SS	6	5,7 <sup>0</sup> <sub>-0,048</sub>	17,0	12,5	0,8	0,5	5,6 <sup>+0,04</sup> <sub>-0,15</sub>	0,7	✓	2,17 €	
CLP-8SS	8	7,6 <sup>0</sup> <sub>-0,058</sub>	21,5	16,5	0,9	0,5	7,4 <sup>+0,06</sup> <sub>-0,18</sub>	0,8	✓	2,40 €	
CLP-10SS	10	9,6 <sup>0</sup> <sub>-0,068</sub>	26,0	20,5	1,1	0,5	9,3 <sup>+0,1</sup> <sub>-0,36</sub>	1,0	✓	2,61 €	
CLP-12SS	12	11,5 <sup>0</sup> <sub>-0,110</sub>	31,0	24,5	1,1	1,0	11,0 <sup>+0,1</sup> <sub>-0,36</sub>	1,0	✓	3,63 €	
CLP-16SS	16	15,2 <sup>0</sup> <sub>-0,110</sub>	40,0	32,5	1,1	1,0	14,7 <sup>+0,1</sup> <sub>-0,36</sub>	1,0	✓	3,60 €	
CLP-20SS	20	19,0 <sup>0</sup> <sub>-0,130</sub>	50,0	40,5	1,3	1,5	18,5 <sup>+0,13</sup> <sub>-0,42</sub>	1,2	✓	9,03 €	

\*Depending on availability - Dimensions in mm

## Our other products



Slat top chain acetal,  
Large range 821



Threaded spherical  
knob, Aluminium



Internal hinge pin for  
aluminium profile,  
Internal hinge pin



T type timing belt, T5  
Steel cored  
polyurethane



Hexagonal nut -  
DIN934, Box set of  
steel nuts



Adjusting nut, Fine  
thread



Accessories, Turntable




Short housing for  
open linear bearing,  
Opened - slim



Drylin® Linear table,  
Maintenance free



Modular cylindrical  
brush, PBT polyester  
bristles



4A motorised linear  
actuator, 4 amperes



Indexing plunger mini,  
miniature - Stainless  
steel

## Complementary products



Clevis components,  
short version,  
Stainless steel - short  
range



Clevis components,  
short version, Steel -  
short range



Male clevis end,  
Stainless steel short