



Protective inserts for combination spanner

Hygienic Usit® and Hygienic Design® CMHDCO CMHDCF


- Protective inserts to be used with the CM combination spanner for mounting Hygienic Usit® and Hygienic Design® products

- Material:

Inserts: AlSi1MgMn

Advantages

- The protective caps have been specifically designed for fastening and un-fastening screwed connections with delicate surfaces.
- The protective caps will safely avoid the risk of contact corrosion with stainless steel screwed connections.
- The inserts are made of aluminium alloy EN AW 602 – a special aluminium suitable for contact with foodstuffs
- The protective cap is safely held in the spanner thanks to its special form and a sprung clip.



DISCOUNTS

Qty	1+	5+	10+
Disc.	Net	-5%	On request

Part N°	For spanner	SW	SW2	A1	B1	ØD1	ØD2	L1	T	T1	H	H1	Price each
													1 to 4
For open-ended spanner													
CM-10/HD/CF	CM-10/HD	10	7	9	17	2,3	-	19,4	5,6	-	8,6	-	18,84 €
CM-11/HD/CF	CM-11/HD	11	8	9	18	2,3	-	20,7	5,7	-	8,7	-	18,84 €
CM-13/HD/CF	CM-13/HD	13	10	10	22	3	-	23,2	6,7	-	10,7	-	19,05 €
CM-16/HD/CF	CM-16/HD	16	13	13	27	3	-	28,6	7,7	-	11,7	-	20,38 €
CM-19/HD/CF	CM-19/HD	19	16	13	30	4	-	32,5	8,6	-	12,6	-	21,54 €
CM-21/HD/CF	CM-21/HD	21	18	13	32	4	-	35,0	9,0	-	13,0	-	21,76 €
CM-27/HD/CF	CM-27/HD	27	24	14	40	4	-	43,8	10,8	-	15,0	-	23,26 €
For ring spanner													
CM-10/HD/CO	CM-10/HD	10	7	-	-	-	17	-	-	8,0	-	11,0	13,11 €
CM-11/HD/CO	CM-11/HD	11	8	-	-	-	18	-	-	9,4	-	11,4	13,11 €
CM-13/HD/CO	CM-13/HD	13	10	-	-	-	21	-	-	11,0	-	13,0	13,80 €
CM-16/HD/CO	CM-16/HD	16	13	-	-	-	25	-	-	12,4	-	14,4	14,15 €
CM-19/HD/CO	CM-19/HD	19	16	-	-	-	30	-	-	14,5	-	16,5	15,33 €
CM-21/HD/CO	CM-21/HD	21	18	-	-	-	32	-	-	14,7	-	16,7	15,43 €
CM-27/HD/CO	CM-27/HD	27	24	-	-	-	41	-	-	17,0	-	19,0	17,30 €

All dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

63

Our other products



ZG1
Plastic spur gear,
Machined plastic
(delrin)



PRFSRAD
Dual lock for
aluminium profile,
Quick fitting, self
locking door du...



BLHB20
Right angled gearbox,
bored shafts, up to
1.77 Nm



CHAR7520
Spring hinge, screwed



NK40
Drylin®N miniature
guiding system, Withd
40 mm



DOMI30
Accessories, Turntable



FDS
Flexible drive shaft,
Masterflex® Steel,
with PVC casing



PP60
Worm and wheel gear
reducer, from 17.80
to 34 Nm



PAT85
Pressed stainless
steel articulating foot
Ø85, Ø 85



PTRSS
Idler chain sprocket,
For hostile
environments



GLT3E-50
Telescopic drawer,



BSCm
Knurled torque knobs
- male, Knurled
threaded torque

Complementary products



CM
Tools Hygienic Usit®
and Hygienic
Design®,
Combination spanner



CM_CO
Tools Hygienic Usit®
and Hygienic
Design®, Protective
inserts for ...