

# Warning chain

## CHN<sub>RB</sub>

With long red and white links


- Steel chain supplied by the box
- Red and white painted steel

### Applications

- Warning, signalling

### Info

- Not to be used for lifting applications



### DISCOUNTS

Qty	1+	3+	10+
Disc.	Net -10%		On request

Part number	Link			Typical working load (kg)	Length per box	Weight per box (kg)	Price each 1 to 2
	ØT	P	E				
CHN-5/RB/B	5	35	10	155	25	10,50	123,13 €

All dimensions in mm

**HPC**

WEB  
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



PVL

Small lobed handle,  
Polyamide



AC

Strike for toggle latch,  
15mm



H0

Crossed helical gear  
crossed axis at 90°,  
Steel 20NCD2



SERB

Universal latch key,  
Universal latch key



DCG

Suction cup, 2.5  
bellows, silicon



PCLA\_M

Technopolymer  
clamping lever -  
female, Plastic



DB

Steel bevel gear, 2:1



CHC

Socket headed screw,  
Steel class 12.19



DIL

Lever operated  
locking bolt, lever  
clamp



AC156-157

Strike for toggle latch,  
25.5mm



HRV

V- rail guidance  
Simple Select®  
system, Rail with



PCF2

Conical flexible  
mount, Oval base  
plate

## Complementary products



CHN\_CHNSS

Straight long link  
chain, Galvanised  
steel



MRA

Quick link, Steel



MAC

Carabiner DIN5299  
steel, Steel



PPC<sub>SS</sub>

Pad eye on mounting  
plate squarred,  
Stainless steel