

Suction cup, 2.5 bellows



DCG

For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural
rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60


DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request


Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NBR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NBR	42,0	46,0	8,0	24,0		-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	SCR30M6	✓	5,60 €
DCG30-SI	32,0	37,5	8,0	23,0		✓	6,19 €
DCG40-SI	42,0	46,0	8,0	24,0		✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NR	42,0	46,0	8,0	24,0		-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

*Depending on availability - Dimensions in mm

Our other products



G1
Steel spur gear, Steel
20NCD2



FRss
Stainless steel thread
inserts, Stainless steel



DOG319
Motor-gearbox 12V
and 24V DC, from 4 to
9 Nm



PTR
Idler chain sprocket,
For standard
applications



SSHBRA
Stainless steel bevel
gear, 1,5:1 2:1 3:1



PITAss
Locking bolt, with T
handle




TSRTC
Stem support for
caster, For swivel
caster with central
hole



SERB
Cam latch, Cam latch




DOMI80
Domino 80 adjustable
slide, Slide DOMILINE



RPP
Connecting plate for
RPP type timing belts,
RPP



DTR
Chain idler sprocket,
Chain idler sprocket -



PF40NM
Worm and wheel gear
reducer, up to 18 Nm

Complementary products



TM_CTM_CTF
Suction cup threaded
insert, Insert for
suction cup - Tread
click-in



SCR
Suction cup threaded
insert, Insert for
suction cup - Socket
screw