

Warning chain

CHN_{RB}

With long red and white links


- Steel chain supplied by the box
- Red and white painted steel

Applications

- Warning, signalling

Info

- Not to be used for lifting applications



DISCOUNTS

Qty	1+	3+	10+
Disc.	Net -10%		On request

Part number	Link ØT	P	E	Typical working load (kg)	Length per box	Weight per box (kg)	Price each 1 to 2
CHN-5/RB/B	5	35	10	155	25	10,50	123,13 €

All dimensions in mm

HPC

WEB
04/2021

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



YG0

HEAVY DUTY spur gear, Steel 35NCD6



CLG2

Moulded plastic spur gear, Moulded plastic (nylon)



CLASS

Stainless steel indexing handle - female, Stainless steel



PSG15

Spur gear - precision range, Stainless steel 303



DOMI120

Accessories, Plate



HTD5M_25

HTD Heavy duty timing pulley, HTD5 Aluminium



DOMI30

Domino 30 adjustable slide, Slide DOMILINE 30



AC156-157

Strike for toggle latch, 25.5mm



DER63

Stainless steel AC asynchronous motor



PSG08

Spur gear - precision range, Pre-hardened



SME

Male rod ends, Stainless steel / PTFE



DCG

Suction cup, 2.5 bellows, nitrile

Complementary products



CHN_CHNSS

Straight long link chain, Galvanised steel



MRA

Quick link, Steel



MAC

Carabiner DIN5299 steel, Steel



PPCcs

Pad eye on mounting plate squarred, Stainless steel