

Suction cup, 2.5 bellows



DCG

For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NBR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NBR	42,0	46,0	8,0	24,0	SCR30M6	-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	✓	5,60 €	
DCG30-SI	32,0	37,5	8,0	23,0	✓	6,19 €	
DCG40-SI	42,0	46,0	8,0	24,0	SCR30M6	✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NR	42,0	46,0	8,0	24,0	SCR30M6	-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

*Depending on availability - Dimensions in mm


Our other products




DB
Steel bevel gear, 2:1



AT5-16ECO
AT type timing pulley,
Economy range - AT5
aluminium



NK80
Drylin®N miniature
guiding system, Width
80mm



CRM
Moulded nylon rack,
Nylon



UCP
Cast iron pillow block
bearing, Cast iron



MRA
Quick link, Steel




BAG0
Locking rings in
stainless steel,
Stainless steel



BG
Oldham coupling,
With set screw



CFUURSS
Cam follower stainless
steel, Standard -



IN1
Internal gear,
Machined plastic



T5M T10M
T type timing belt per
metre, T10 Steel



RVM25
Manually operated
gearbox, Bevel

Complementary products



SCR
Suction cup threaded
insert, Insert for
suction cup - Socket
screw



TM_CTM_CTF
Suction cup threaded
insert, Insert for
suction cup - Tread
click-in