

Suction cup, 2.5 bellows



DCG

For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural
rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NBR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NBR	42,0	46,0	8,0	24,0		-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	SCR30M6	✓	5,60 €
DCG30-SI	32,0	37,5	8,0	23,0		✓	6,19 €
DCG40-SI	42,0	46,0	8,0	24,0		✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NR	42,0	46,0	8,0	24,0		-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

*Depending on availability - Dimensions in mm

Our other products



BFM2

Flanged bronze nut,
Bronze - 2 threads



LC

Friction clutch, 190 to
1800 Nm



P20

Worm and wheel gear
reducer, up to 5 Nm



RIMple

Locking castor, with
mounting plate



RT61ss

Self-centering locking
Assembly,
Medium/low torque



CSSSS

Stainless steel
spherical bearing,
Stainless steel / PTFE




CCLSS

Stainless steel wire
thimble, Stainless
steel



SCH

Horizontal hook
toggle clamp,
Horizontal Hook
clamp - stainless steel



M1

Worm and wheel set,
Machined plastic
(delrin)



CNA-CNG

Right angled
mounting plate, Right
angled mounting



NDS20

Double cross clamp,
Crossed



PPF

Indexing plunger with
flange, with drilled
flange

Complementary products



SCR

Suction cup threaded
insert, Insert for
suction cup - Socket
screw



TM_CTM_CTF

Suction cup threaded
insert, Insert for
suction cup - Tread
click-in