

# Straight long link chain

Ste

CHN Conforms to NFE26020 and DIN5685C




- Galvanised steel chain, supplied by the box

## Applications

- Rigging, safety barriers, signage

## Info.

- Under no circumstances should this type of chain be used for lifting



## DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-10%	-15%	On request

Part number	Chain ØT	P	E	Max carrying load (kg)	Length / Box (m)	Weight / Box (kg)	Stock*	Price each 1 to 2
CHN-2/B	2,0	22	4	25	25	1,56	✓	23,03 €
CHN-2.5/B	2,5	24	5	40	25	2,53	-	26,34 €
CHN-3/B	3,0	26	6	60	25	3,70	✓	32,48 €
CHN-3.5/B	3,5	28	7	75	25	5,30	-	41,83 €
CHN-4/B	4,0	32	8	100	25	6,70	✓	48,06 €
CHN-4.5/B	4,5	34	9	125	25	8,90	-	58,67 €
CHN-5/B	5,0	35	10	155	25	10,00	✓	64,10 €
CHN-6/B	6,0	42	12	230	25	15,70	-	100,18 €
CHN-7/B	7,0	49	14	300	25	21,40	-	136,72 €
CHN-8/B	8,0	52	16	400	10	11,60	-	70,54 €

\*Depending on availability - Dimensions in mm

# Sta Straight long link stainless steel chain

Conforms to NFE26020 and DIN5685C CHNss


- Stainless steel chain, supplied by the box

## Applications

- Rigging, safety barriers, signage

## Info.

- Under no circumstances should this type of chain be used for lifting



## DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Chain ØT	P	E	Max carrying load (kg)	Length / Box (m)	Weight / Box (kg)	Stock*	Price each
CHN-2/SS/B	2,0	22	4	25	25	1,49	✓	76,94 €
CHN-2.5/SS/B	2,5	24	5	40	25	2,54	✓	113,35 €
CHN-3/SS/B	3,0	26	6	60	25	3,74	✓	162,75 €
CHN-4/SS/B	4,0	32	8	100	25	6,83	✓	272,37 €
CHN-5/SS/B	5,0	35	10	155	25	10,64	-	424,91 €
CHN-6/SS/B	6,0	42	12	230	25	15,62	-	621,44 €
CHN-8/SS/B	8,0	52	16	400	10	11,28	-	424,91 €

\*Depending on availability - Dimensions in mm