

Suction cup, 2.5 bellows



DCG For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NBR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NBR	42,0	46,0	8,0	24,0	SCR30M6	-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	✓	5,60 €	
DCG30-SI	32,0	37,5	8,0	23,0	✓	6,19 €	
DCG40-SI	42,0	46,0	8,0	24,0	SCR30M6	✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NR	42,0	46,0	8,0	24,0	SCR30M6	-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €


*Depending on availability - Dimensions in mm

Our other products



TIFss

Threaded stud -
DIN976A, Stainless
steel




ACLBTS

Closing system for
aluminium profile, 90°
bracket for spherical
end...



UTKpwrr

V shaped channel
UtiliTrak®, V rail



M0

Worm and wheel set,
Machined plastic
(delrin)



DFG

Flat suction cup,
silicon



PGNT

Thermoplastic T
handle. With threaded
spindle



MEB

Moulded plastic bevel
gear (nylon), 1:1



LWH

High rigidity linear
slide, Rail - from 9320
N to 71300 N



ETQ

Magnetic label holder
for aluminium profile,



SVT5

Screwjack with
travelling screw, with



PTA50

Articulated levelling
foot, pressed base



DOMI_MD

Domino rotary table,
40/1

Complementary products



TM_CTM_CTF

Suction cup threaded
insert, Insert for
suction cup - Tread
click-in



SCR

Suction cup threaded
insert, Insert for
suction cup - Socket
screw