

Suction cup, 2.5 bellows



DCG For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NBR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NBR	42,0	46,0	8,0	24,0	SCR30M6	-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	✓	5,60 €	
DCG30-SI	32,0	37,5	8,0	23,0	✓	6,19 €	
DCG40-SI	42,0	46,0	8,0	24,0	SCR30M6	✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	-	4,61 €	
DCG30-NR	32,0	37,5	8,0	23,0	-	5,00 €	
DCG40-NR	42,0	46,0	8,0	24,0	SCR30M6	-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

*Depending on availability - Dimensions in mm

Our other products



PTA100
Articulated levelling foot, pressed base Ø100, Ø 100



UTKswr
Utilitak® V rail, V rail



DBL820
Idler for slat top chain, Ranges 820 and 815



BPM
Stainless steel slotted spring plunger with ceramic ball tip, 303 St...



CHB
Worm and wheel gear reducer, up to 22 Nm



BPFL
Sheet steel flanged bearing for light loads, Sheet steel



WW20
Drylin® W slide, slide assembly



CFUURSS
Cam follower stainless steel, Standard - stainless steel



TBL
Mini leadscrew table with metric thread, 1kg



RBGpl
Swivel castor with double brake, Steel - grey rubber



FBL6000_K13
Brush strip per meter PP fibres Ø0.2, Black striated polypropylene



PLC_PLT
Magnetic stud with threaded hole, With threaded hole

Complementary products



TM_CTM_CTF
Suction cup threaded insert, Insert for suction cup - Tread click-in



SCR
Suction cup threaded insert, Insert for suction cup - Socket screw