



Socket with protective insert

Hygienic Design® and Usit®

DEP-HD

- Socket with protective plastic insert for mounting Hygienic Design® and Usit® products


- Materials:

Socket: tool steel

Insert: special PETP


Advantages

- 1/2" drive socket with a plastic insert to tighten and loosen screws and nuts in the Hygienic range. The plastic insert is made of special PETP and is FDA approved. The inserts are pressed into the socket by hand. Their special shape, combined with a clamping device, ensures optimal retention inside the socket.
- No special tools are required to replace worn plastic inserts.
- With a tightening torque (according to DIN standard for A4-70 screws and nuts, friction coefficient 0.12 μ) the inserts plastic have a life span of up to 1,000 cycles or more.



□12,5(1/2")

DEP/HD socket



DEP/HD/INS insert

DISCOUNTS

Qty	1+	5+	10+
Disc	Net	-5%	On request

Part N°	ØD	ØD1	L	T	SW	SW1	Suitable for hexagonal screw	Price each
								1 to 4
Socket								
DEP-11/HD	16,6	22	37,3	10,1	11	-	-	25,65 €
DEP-13/HD	19,1	22	37,3	10,6	13	-	-	25,52 €
DEP-16/HD	22,9	23,6	37,1	11,3	16	-	-	26,87 €
DEP-19/HD	26,6	23	37,0	13,2	19	-	-	27,77 €
DEP-21/HD	29,0	25	36,8	12,9	21	-	-	43,21 €
DEP-27/HD	35,2	25	44,4	18,1	27	-	-	51,06 €
Protective insert								
DEP-8/HD/INS	-	-	18,0	6	11	8	M5	8,45 €
DEP-10/HD/INS	-	-	19,5	10	13	10	M6	8,52 €
DEP-13/HD/INS	-	-	21,5	11	16	13	M8	9,35 €
DEP-16/HD/INS	-	-	22,0	13,5	19	16	M10	9,82 €
DEP-18/HD/INS	-	-	21,5	12	21	18	M12	10,16 €
DEP-24/HD/INS	-	-	26,5	18	27	24	M16	14,51 €

All dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax


cial2@hpceurope.com

HPC

SUPPLEMENT 2019

61

Our other products



PM2

Worm and wheel set,
Machined plastic
(delrin)



PCS_PA6

Plastic sprocket,
12.7mm (DIN 08B-1)



TBEBASE

Base plate for
economic mini-table,
Allows X-Y cross
tables



VLBS

Folding lifting ring for
welding, Folding - for
welding



E30

Right angle helical
reducers, from 1.50 to
9 Nm



HAS

Captive C washer,
Slotted flat headed
shoulder screw



AT10courroie

AT type timing belt,
AT10 Steel cored
polyurethane



GE_ES_2RS

Spherical bushing,
Steel / steel with seals



SRG

Adjustable latch
clamp with strike
plate, Stroke from
78mm to 90mm



BAC105

Storage bin, 8mm



UGAC_UGET

Actuator guide kit,
Coupling for threaded
cylinder end



SCH

Horizontal hook
toggle clamp,
Horizontal Hook
clamp - stainless steel

Complementary products



EBC

Cap nut Hygienic
Design®, Compact



VHTM

Hexagonal headed
screw Hygienic
Design®, Stainless
steel