

### - Materials:

Steel version

Body : steel (class 5.8)

Pin: hardened steel

Stainless steel version

Body: stainless steel 303

Pin: Hardened stainless steel 420

Ring: Stainless steel 301

### - Finish: Steel version

Pin: hardened, ground and blackened

Stainless steel version


Pin : hardened , polished and ground




### Info.

- Index bolts are used whenever lateral movement needs to be blocked. Once released, another position can be set.

- The ring allows the unlocking action to be automated; by using pneumatic cylinder for example or some other remote control mechanism.



Typical application



### DISCOUNTS

|       |      |      |            |
|-------|------|------|------------|
| Qty   | 1+   | 6+   | 20+        |
| Disc. | List | -10% | On request |

| Part number  | ØD | ØD1     | ØD4 | L1 | L2 | L4 | H  | SW1 | SW2 | F <sub>x30°</sub> | Spring strength |        |        | Price each 1 to 5 |
|--|----|---------|-----|----|----|----|----|-----|-----|-------------------|-----------------|--------|--------|-------------------|
|  |    |         |     |    |    |    |    |     |     |                   | F1 (N)          | F2 (N) | Stock* |                   |
| <b>Steel, hardened steel pin</b>                     |    |         |     |    |    |    |    |     |     |                   |                 |        |        |                   |
| DIA8-4   | 4  | M8x1,0  | 15  | 15 | 6  | 13 | 4  | 10  | 13  | 1,0               | 6               | 12     | ✓      | 9,69 €            |
| DIA10-5  | 5  | M10x1,0 | 23  | 17 | 7  | 15 | 5  | 13  | 17  | 1,3               | 5               | 12     | ✓      | 9,23 €            |
| DIA12-6  | 6  | M12x1,5 | 23  | 20 | 8  | 17 | 6  | 14  | 19  | 1,8               | 6               | 14     | ✓      | 10,25 €           |
| DIA16-8  | 8  | M16x1,5 | 28  | 26 | 10 | 23 | 8  | 19  | 24  | 2,3               | 15              | 35     | ✓      | 13,66 €           |
| DIA20-10   | 10 | M20x1,5 | 28  | 28 | 12 | 25 | 10 | 22  | 30  | 2,8               | 15              | 40     | ✓      | 19,45 €           |
| <b>Stainless steel, hardened stainless steel pin</b> |    |         |     |    |    |    |    |     |     |                   |                 |        |        |                   |
| DIA8-4/SS  | 4  | M8x1,0  | 15  | 15 | 6  | 13 | 4  | 10  | 13  | 1,0               | 6               | 12     | ✓      | 16,95 €           |
| DIA10-5/SS   | 5  | M10x1,0 | 23  | 17 | 7  | 15 | 5  | 13  | 17  | 1,3               | 5               | 12     | ✓      | 16,15 €           |
| DIA12-6/SS   | 6  | M12x1,5 | 23  | 20 | 8  | 17 | 6  | 14  | 19  | 1,8               | 6               | 14     | ✓      | 18,98 €           |
| DIA16-8/SS   | 8  | M16x1,5 | 28  | 26 | 10 | 23 | 8  | 19  | 24  | 2,3               | 15              | 35     | ✓      | 25,35 €           |
| DIA20-10/SS  | 10 | M20x1,5 | 28  | 28 | 12 | 25 | 10 | 22  | 30  | 2,8               | 15              | 40     | ✓      | 41,90 €           |

\*Depending on availability - Dimensions in mm

## Our other products



FBL6000\_K1

Brush strip per meter  
PA6 fibres Ø0.2 to  
Ø0.3, Black polyamide  
6 -...



GLB

Small 6 lobe female  
handle,  
Technopolymer -  
Brass



VPRA\_M

Handwheel with  
handle,  
Thermosetting plastic  
- stainless steel hub



UCFL\_PBT

Stainless  
steel/Polymer flanged  
bearing, Polymer and  
stainless steel



AC144

Strike for toggle latch,  
22mm



GP75

Spring loaded toggle  
latch, Standard  
(GP75)




PRF\_GAL

Roller for aluminium  
profile, Fixing kit for  
roller concentric



BVR

Adjustable screw stop,  
Steel



PRF\_PIV

Internal hinge pin for  
aluminium profile,  
Internal hinge pin



VB

Small 6 lobe threaded  
handle - female,  
Duroplast - Stainless



SER

Magnetic doorstop for  
aluminium profile,  
Magnetic doorstop



PTA150

Articulated levelling  
foot, pressed base  
Ø150, Ø150

## Complementary products



SDA

Locking bolt support  
bracket, Mounting  
holes parallel to  
locating bolt



SDB

Locking bolt support  
bracket, Mounting  
holes at 90° to  
locating bolt



PITAss

Locking bolt, with T  
handle



PITAss

Locking bolt, with T  
handle