

- Materials:

Steel version

Body : steel (class 5.8)

Pin: hardened steel

Stainless steel version

Body: stainless steel 303

Pin: Hardened stainless steel 420

Ring: Stainless steel 301

- Finish: Steel version

Pin: hardened, ground and blackened

Stainless steel version


Pin : hardened , polished and ground




Info.

- Index bolts are used whenever lateral movement needs to be blocked. Once released, another position can be set.

- The ring allows the unlocking action to be automated; by using pneumatic cylinder for example or some other remote control mechanism.



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD4	L1	L2	L4	H	SW1	SW2	Fx30°	Spring strength			Price each 1 to 5
											F1 (N)	F2 (N)	Stock*	
Steel, hardened steel pin														
DIA8-4	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	9,69 €
DIA10-5	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	9,23 €
DIA12-6	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	10,25 €
DIA16-8	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	13,66 €
DIA20-10	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	19,45 €
Stainless steel, hardened stainless steel pin														
DIA8-4/SS	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	16,95 €
DIA10-5/SS	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	16,15 €
DIA12-6/SS	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	18,98 €
DIA16-8/SS	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	25,35 €
DIA20-10/SS	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	41,90 €

*Depending on availability - Dimensions in mm

Our other products



T10_21N1F

T type timing pulley,
Economy range - T10
moulded plastic
(nylon)



T10-BAR

T type tooth bar
stock, T10



PCS8ECO

Chain sprocket - steel,
8mm (DIN 05B-1)



BIM

Indexing plunger mini,
miniature



PCP

Cell carrier assembly,
Ready assembled



GP

Spring loaded toggle
latch, With padlock-
holder



GPBSS

Threaded spherical
knob, Stainless steel
304



GAL_25

Ø25 conveyor roller,
Without ball bearing



PCS37

Chain sprocket - steel,
9.525mm (DIN06B-1)



CDC

Conical compression
spring, Conical



BMF

Knurled knob -
female, Knurled -



GE

Toggle latches,
Miniature

Complementary products



SDA

Locking bolt support
bracket, Mounting
holes parallel to
locating bolt



SDB

Locking bolt support
bracket, Mounting
holes at 90° to
locating bolt



BIM

Indexing plunger mini,
miniature



PITA

Locking bolt, with T
handle