

Domino 30 adjustable slide



DOMI30

For C1 loads up to 150 N




- Suitable for heavy loads
- Low coefficient of friction
- High quality slideways
- Low backlash system
- Very fine adjustment (0.05mm)
- Standard axis lengths
- Simple control system

Applications


- Fine adjustment of brazing/welding heads or plasma cutting heads
- Inkjet printer head positioning
- Camera positioning
- Machine parts positioning (milling head, milling spindles,...)
- Burner focusing
- Laser head positioning
- Moving stops
- Centred movement for lateral guidance (slide with left-right pin)




Options

- Other stroke lengths available, please contact us for details
- If a digital counter is required to be fitted to the linear slide, replace /XY by Z in the part number



DOMI30-CV Adjustable slide fitted with handwheel and counter





DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request


Part number	LA	LI	Stroke (mm)	Pitch (mm)	C1 (N)	C2 (N)	Maximum loads				Price each
							FA (N)	Mx (Nm)	My (Nm)	Mz (Nm)	
Slide only											
DOMI30-5	45	50	5	0,5	150	65	40	2	2	1	415,54 €
DOMI30-10	45	55	10	0,5	150	65	40	2	2	1	424,11 €
DOMI30-15	45	60	15	0,5	150	65	40	2	2	1	436,96 €
DOMI30-20	45	65	20	0,5	150	65	40	2	2	1	445,53 €
Slide with counter and handwheel											
DOMI30-5-CV/XY	45	50	5	0,5	150	65	40	2	2	1	730,42 €
DOMI30-10-CV/XY	45	55	10	0,5	150	65	40	2	2	1	738,99 €
DOMI30-15-CV/XY	45	60	15	0,5	150	65	40	2	2	1	751,84 €
DOMI30-20-CV/XY	45	65	20	0,5	150	65	40	2	2	1	760,41 €

Dimensions in mm




DOMI30 For Domino 30 adjustable slides


- The **fastening kit** is used to attach the DOMINO adjustable slide to its mounting surface.
- The **machineable mounting plate** allows you to attach other equipment to the adjustable slide.




Tool plate support




Assembly angle bracket



DOMI30-B fastening set



Typical application




DOMI30-M mounting plate



Fastening set
DOMI30-B



Mounting plate
DOMI30-M



Turntable
DOMI30-PT

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request


Part number	Type	Price each
DOMI30-B	Fastening set	23,56 €
DOMI30-M	Mounting plate	64,26 €
DOMI30-PT	Rotary turntable	359,85 €

Dimensions in mm



For Domino 30 adjustable slides **DOMI30**


- **Connecting kits** are used to join two DOMINO adjustable slides.




Connecting kit
DOMI30-XY




Connecting kit DOMI30-XY




X-Y connecting kit




Connecting kit
DOMI 30-XZ



X-Z connecting kit



Typical application



Connecting kit
DOMI30-XZ


DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Type	Price each
DOMI30-XY	Connecting kit X-Y	57,83 €
DOMI30-XZ	Connecting kit X-Z	66,40 €

Dimensions in mm

Our other products



PTBss

Threaded eye hook
stainless steel,
Stainless steel



UTKpwr

Utilitak® V rail, V rail



WINGbrEcrou

Manually tightened
wing nut DIN315,
Brass DIN 315



DOMI120

Domino 120
adjustable slide, Slide
DOMILINE 120 with
counter and han...




SLS

Bearing block for
leadscrew, Floating
Drylin® bearing block




AC

Strike for toggle latch,
12,13,18 and 20mm




CHNrb

Warning chain with
red and white links,
Steel



T5M T10M

T type timing belt per
metre, T10 Steel
cored polyurethane



RPP14

RPP heavy duty
timing belt, RPP14



UGAC_UGET

Connection for
threaded actuator
rod, Connection for



MSP19

Masterplate®
glueable insert Ø19,
Cylindrical with



RFK38C

Hypoid gearbox -
Stainless steel, up to
200 Nm

Complementary products



DOMI30

Domino 30 adjustable
slide, Slide DOMILINE
30



DOMI30

Accessories, Plate



DOMI30

Domino 30 adjustable
slide, Slide DOMILINE
30 with counter and
handw...