

# Clevis and clip, short version




CLSSs  
CLPSSs


With **stainless steel** circlips

- Trunnion link
- Material: stainless steel 303
- To DIN 71752, DIN 471-UNI7435
- Spring clip supplied with 2 circlips

Clevis CLS-SS



Clip CLP-SS



End fitting

stainless steel



Clip CLP-SS



CLS-SS



CLP-SS

## DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-10%	-20%	On request

Part number	Ød2 (6H)	b1 (B13)	a1 (h11)	a2	Ød1 (h9)	d3 <sup>+0,3</sup>	L1 <sup>+0,2</sup>	L3 <sup>+0,5</sup>	L2 <sup>+0,3</sup>	g <sup>+0,5</sup>	Static load Co (daN)	Stock*	Price each 1 to 5
												✓	€
CLS-5SS	M5	5	10	10 <sup>+0,30 -0,16</sup>	5	9	7,5	26	20	10	500	✓	6,36 €
CLS-6SS	M6	6	12	12 <sup>+0,30 -0,16</sup>	6	10	9,0	31	24	12	720	✓	6,82 €
CLS-8SS	M8	8	16	16 <sup>+0,30 -0,16</sup>	8	14	12,0	42	32	16	1280	✓	11,47 €
CLS-10CSS	M10x1,25	10	20	20 <sup>+0,30 -0,16</sup>	10	18	15,0	52	40	20	-	✓	26,47 €
CLS-12SS	M12x1,75	12	24	24 <sup>+0,30 -0,16</sup>	12	20	18,0	62	48	24	2880	✓	34,49 €
CLS-16CSS	M16x1,5	16	32	32 <sup>+0,30 -0,16</sup>	16	26	24,0	83	64	32	-	✓	81,44 €
CLS-20CSS	M20x1,5	20	40	40 <sup>+0,50 -0,20</sup>	20	34	30,0	105	80	40	-	-	On request

## Trunnion clip

Références	Ød1 (h11)	d2	L <sup>+0,3</sup>	LH <sup>+0,3</sup>	m (H13)	e	Ød3	s (h11)	Circlip size	Stock*	Price each. 1 to 5
										✓	€
CLP-5SS	5	4,8 <sup>0 -0,048</sup>	15,0	10,5	0,7	0,5	4,7 <sup>+0,04 -0,15</sup>	0,6	0,6	✓	2,23 €
CLP-6SS	6	5,7 <sup>0 -0,048</sup>	17,0	12,5	0,8	0,5	5,6 <sup>+0,04 -0,15</sup>	0,7	0,7	✓	2,17 €
CLP-8SS	8	7,6 <sup>0 -0,058</sup>	21,5	16,5	0,9	0,5	7,4 <sup>+0,06 -0,18</sup>	0,8	0,8	✓	2,40 €
CLP-10SS	10	9,6 <sup>0 -0,068</sup>	26,0	20,5	1,1	0,5	9,3 <sup>+0,1 -0,36</sup>	1,0	1,0	✓	2,61 €
CLP-12SS	12	11,5 <sup>0 -0,110</sup>	31,0	24,5	1,1	1,0	11,0 <sup>+0,1 -0,36</sup>	1,0	1,0	✓	3,63 €
CLP-16SS	16	15,2 <sup>0 -0,110</sup>	40,0	32,5	1,1	1,0	14,7 <sup>+0,1 -0,36</sup>	1,0	1,0	✓	3,60 €
CLP-20SS	20	19,0 <sup>0 -0,130</sup>	50,0	40,5	1,3	1,5	18,5 <sup>+0,13 -0,42</sup>	1,2	1,2	✓	9,03 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF-CHAR-POU

Tool holder for aluminium profile, Moveable tool holder




P45

Worm and wheel gear reducer, up to 40 Nm



VR5Sss

Male swivelling lifting rings stainless steel, Male swivelling - s...




M2

Worm and wheel set, Bronze



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW



CFC

Spring loaded position switch, Electric contact



BSM

Spring plunger with internal hexagonal socket, steel body, plastic pin



TFR

Rigid manual tensioner, Fixed




BOX-TOR-DRING

Box set of Nitrile D-rings NBR90Sh A, Flange seals



PHTss

Pull handle, Up to 250 °C



PRF\_PSA

Shaft support for aluminium profile, Shaft stop



PLM-C

Cylindrical holding magnets, Cylindrical holding magnet

## Complementary products



CLSCLP\_SS

Clevis components, short version, Stainless steel - short range



CLSCLP

Clevis components, short version, Steel - short range



CLM

Male clevis end, Stainless steel short