

Clevis and clip, short version




CLSSs
CLPSSs


With **stainless steel** circlips

- Trunnion link
- Material: stainless steel 303
- To DIN 71752, DIN 471-UNI7435
- Spring clip supplied with 2 circlips

Clevis CLS-SS



Clip CLP-SS



End fitting

stainless steel



Clip CLP-SS



CLS-SS



CLP-SS

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-10%	-20%	On request

Part number	Ød2 (6H)	b1 (B13)	a1 (h11)	a2	Ød1 (h9)	d3 ^{+0,3}	L1 ^{+0,2}	L3 ^{+0,5}	L2 ^{+0,3}	g ^{+0,5}	Static load Co (daN)	Stock*	Price each 1 to 5
												✓	€
CLS-5SS	M5	5	10	10 ^{+0,30} _{-0,16}	5	9	7,5	26	20	10	500	✓	6,36 €
CLS-6SS	M6	6	12	12 ^{+0,30} _{-0,16}	6	10	9,0	31	24	12	720	✓	6,82 €
CLS-8SS	M8	8	16	16 ^{+0,30} _{-0,16}	8	14	12,0	42	32	16	1280	✓	11,47 €
CLS-10CSS	M10x1,25	10	20	20 ^{+0,30} _{-0,16}	10	18	15,0	52	40	20	-	✓	26,47 €
CLS-12SS	M12x1,75	12	24	24 ^{+0,30} _{-0,16}	12	20	18,0	62	48	24	2880	✓	34,49 €
CLS-16CSS	M16x1,5	16	32	32 ^{+0,30} _{-0,16}	16	26	24,0	83	64	32	-	✓	81,44 €
CLS-20CSS	M20x1,5	20	40	40 ^{+0,50} _{-0,20}	20	34	30,0	105	80	40	-	-	On request

Trunnion clip

Références	Ød1 (h11)	d2	L ^{+0,3}	LH ^{+0,3}	m (H13)	e	Ød3	s	Circlip size (h11)	Stock*	Price each. 1 to 5
										✓	€
CLP-5SS	5	4,8 ⁰ _{-0,048}	15,0	10,5	0,7	0,5	4,7 ^{+0,04} _{-0,15}	0,6	0,6	✓	2,23 €
CLP-6SS	6	5,7 ⁰ _{-0,048}	17,0	12,5	0,8	0,5	5,6 ^{+0,04} _{-0,15}	0,7	0,7	✓	2,17 €
CLP-8SS	8	7,6 ⁰ _{-0,058}	21,5	16,5	0,9	0,5	7,4 ^{+0,06} _{-0,18}	0,8	0,8	✓	2,40 €
CLP-10SS	10	9,6 ⁰ _{-0,068}	26,0	20,5	1,1	0,5	9,3 ^{+0,1} _{-0,36}	1,0	1,0	✓	2,61 €
CLP-12SS	12	11,5 ⁰ _{-0,110}	31,0	24,5	1,1	1,0	11,0 ^{+0,1} _{-0,36}	1,0	1,0	✓	3,63 €
CLP-16SS	16	15,2 ⁰ _{-0,110}	40,0	32,5	1,1	1,0	14,7 ^{+0,1} _{-0,36}	1,0	1,0	✓	3,60 €
CLP-20SS	20	19,0 ⁰ _{-0,130}	50,0	40,5	1,3	1,5	18,5 ^{+0,13} _{-0,42}	1,2	1,2	✓	9,03 €

*Depending on availability - Dimensions in mm

Our other products



GP75

Spring loaded toggle latch, Standard (GP75)



SSE

Stainless steel spherical bearing, Stainless steel / PTFE



WING

Manually tightened wing nut, Stainless steel DIN 314/315



RJUM05

Drylin R® linear bearing housing, Closed - Slim



M1

Worm and wheel set, Machined plastic (delrin)



HAS

Captive C washer, Slotted flat headed shoulder screw



PW_PWG25

Wheel - precision range, Bronze



T5P_T10P

Connecting plate for T type timing belts, T10



RPC

Wheel, Polyamide



NPTF20

Fixed tube carrier, Fixed Ø10 to Ø14



NSU

Universal 90° support clamp, Universal 90°



CHAL3

Piano hinge, Aluminium

Complementary products



CLSCLP_SS

Clevis components, short version, Stainless steel - short range



CLSCLP

Clevis components, short version, Steel - Short range