

- **Very high deformation allows high levels of energy to be absorbed.**
- Progressive deformation
- Materials:
 - Core: Stainless steel plates (A2)
 - Head: Rubber
- **Hardness: NK 55-60 Shore A**
- Working temp: -40°C to +70°C


Uses

- Shock absorbing stop

Info.

- **Not sold individually, please contact us for details**
- Load and stiffness figures are given as a guide only

stainless steel



DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	T	Compression Stiffness (N/mm)	Max load (N)	Stock*	Price each 1 to 5
D-ZY4-10-10/SS	M4	10	10	10	38	43	✓	1,70 €
D-ZY4-15-8/SS	M4	15	8	10	122	95	✓	3,00 €
D-ZY4-15-10/SS	M4	15	10	10	106	95	✓	2,06 €
D-ZY4-15-15/SS	M4	15	15	10	74	95	✓	2,26 €
D-ZY6-20-15/SS	M6	20	15	18	138	170	✓	2,96 €
D-ZY6-20-20/SS	M6	20	20	18	-	-	✓	3,05 €
D-ZY6-20-25/SS	M6	20	25	18	-	-	✓	2,87 €
D-ZY6-25-10/SS	M6	25	10	18	-	-	✓	2,63 €
D-ZY6-25-15/SS	M6	25	15	18	254	280	✓	2,92 €
D-ZY6-25-20/SS	M6	25	20	18	128	280	✓	3,25 €
D-ZY6-25-25/SS	M6	25	25	18	-	-	✓	3,57 €
D-ZY6-25-30/SS	M6	25	30	18	80	280	✓	3,85 €
D-ZY8-30-20/SS	M8	30	20	20	200	400	✓	4,36 €
D-ZY8-30-25/SS	M8	30	25	20	-	-	✓	4,81 €
D-ZY8-30-30/SS	M8	30	30	20	120	400	✓	5,42 €
D-ZY8-30-40/SS	M8	30	40	20	-	-	✓	6,40 €
D-ZY8-40-20/SS	M8	40	20	23	-	-	✓	5,95 €
D-ZY8-40-30/SS	M8	40	30	23	23	234	✓	6,66 €
D-ZY8-40-40/SS	M8	40	40	23	-	-	✓	7,02 €
D-ZY10-40-30/SS	M10	40	30	28	-	-	✓	6,70 €
D-ZY10-50-20/SS	M10	50	20	28	680	1000	✓	9,03 €
D-ZY10-50-30/SS	M10	50	30	28	425	1000	✓	9,22 €
D-ZY10-50-40/SS	M10	50	40	28	-	-	✓	10,11 €
D-ZY10-50-45/SS	M10	50	45	28	-	-	-	10,81 €
D-ZY10-50-50/SS	M10	50	50	28	-	-	✓	11,89 €
D-ZY10-60-40/SS	M10	60	40	28	-	-	-	17,48 €
D-ZY10-70-45/SS	M10	70	45	28	-	-	-	22,57 €
D-ZY12-60-40/SS	M12	60	40	33	-	-	✓	17,48 €
D-ZY12-75-25/SS	M12	75	25	37	2000	2300	✓	16,61 €
D-ZY12-75-40/SS	M12	75	40	37	810	2300	-	24,96 €
D-ZY12-75-50/SS	M12	75	50	37	-	-	-	26,08 €
D-ZY12-75-55/SS	M12	75	55	37	-	-	-	27,31 €
D-ZY16-100-25/SS	M16	100	25	41	-	-	-	40,10 €
D-ZY16-100-50/SS	M16	100	50	41	1578	4200	-	53,22 €
D-ZY16-100-55/SS	M16	100	55	41	860	4200	-	55,10 €

*Depending on availability - Dimensions in mm

Our other products



M1
Worm and wheel set,
Machined plastic
(delrin)



OPFL_OPPM
Numerical counter
accessories, Locking
clamp



RAGFLOWsupport
Floway2® Roller track
accessory, Roller
track support



UCP_PBT
Stainless/Polymer
pillow block bearing,
Polymer and stainless
steel



DB
Steel bevel gear, 2:1



MSP19
Masterplate®
glueable insert
Ø19/Ø20, Cylindrical
with nut



WSSss
Symmetrical S shaped
hook stainless steel,
Stainless steel



PPF
Indexing plunger with
flange, with drilled
flange



TBD
Manual leadscrew
table with opposing



BPHT
Ball transfer unit bolt
fitting, Heavy



RTE
Rotex®, jaw coupling,
cast iron




HG5-ECO
Eco range Spur gear,
Steel C45

Complementary products



DZY
Cylindrical stop, Steel



EZYSS
Stainless steel
cylindrical stop,
stainless steel