


Right angle helical gearbox



E15



Torque up to 2.53Nm

- Ratios from 1 :1 to 40:1
- Single piece construction
- Output backlash : $\leq 45'$ (0,75°)
- Max input speed : up to 4000rpm
- Materials :
 - Casing: anodised aluminium
 - Gears/worms : high carbon steel
- Ratios 1:1 to 5:1, Input and output: high carbon steel
- Ratios $\geq 8:1$, Input :high carbon steel, Output : bronze
- Weight: 0.255 kg



Option

- Can be modified to your specifications



OUTPUT TORQUE (Nm values given as a guide only)

Ratios	1:1	2:1	3:1	4:1	5:1	8:1	10:1	20:1	40:1
3000	0,40	0,40	0,40	0,40	0,40	-	-	0,90	1,00
2000	0,46	0,46	0,46	0,46	0,46	0,69	0,79	1,08	1,19
1000	0,66	0,66	0,66	0,66	0,86	0,86	0,97	1,47	1,56
500	0,92	0,92	0,92	0,92	0,92	1,27	1,37	1,87	1,95
100	1,19	1,19	1,19	1,19	1,19	1,72	1,78	2,18	2,24
50	1,25	1,25	1,25	1,25	1,25	1,95	2,07	2,51	2,53
10	1,32	1,32	1,32	1,32	1,32	2,39	2,44		


DISCOUNTS

Qty	1+	2+	4+	10+
Disc.	List -10%	List -15%	On request	On request

Part number	Ratio	Type	Input	Efficiency at 1000 rpm	Max input speed (rpm)	Reflected inertia at input (kg.m ²)	Static self-locking output	Price each
E15-1	1:1	Helical	A	88%	4000	3,762 x 10 ⁻⁶	NO	483,30 €
E15-2	2:1	Helical	A	86%	4000	2,349 x 10 ⁻⁶	NO	483,30 €
E15-3	3:1	Helical	A	85%	4000	2,011 x 10 ⁻⁶	NO	483,30 €
E15-4	4:1	Helical	A	84%	4000	1,986 x 10 ⁻⁶	NO	483,30 €
E15-5	5:1	Helical	A	80%	4000	1,544 x 10 ⁻⁶	NO	483,30 €
E15-8	8:1	Worm+wheel	A	80%	2000	1,622 x 10 ⁻⁶	NO	483,30 €
E15-10	10:1	Worm+wheel	A	73%	2000	1,609 x 10 ⁻⁶	NO	483,30 €
E15-20	20:1	Worm+wheel	A	67%	2000	1,593 x 10 ⁻⁶	YES	483,30 €
E15-40	40:1	Worm+wheel	A	60%	2000	1,589 x 10 ⁻⁶	YES	483,30 €
E15-SP	1:1 - 40:1	Ratio from 1:1 to 40:1						On request
E15-SPA	1:1 - 40:1	Reduced output backlash $\leq 30'$						On request
E15-SPLH	1:1 - 40:1	Left handed						On request

Dimensions in mm

- Ratios from 1:1 to 40:1
- Single piece construction
- Output backlash $\leq 45'$ ($0,75^\circ$)
- Max. input speed up to 4000 rpm
- Materials:
 - Casing: anodised aluminium
 - gears and worms: case-hardened steel
- Ratios 1:1 to 5:1, input and output: case-hardened steel
- Ratios $\geq 8:1$, input: case-hardened steel output: bronze
- Weight: 0.255 kg





Options

- Can be modified to your specifications

Accessories

- Input or output shafts
- E-X and E-DX (tome 2 p.183)



OUTPUT TORQUE (Nm values given as a guide only)

Ratios	1:1	2:1	3:1	4:1	5:1	8:1	10:1	20:1	40:1
3000	0,60	0,60	0,60	0,60	0,60	-	-	-	-
2000	0,70	0,70	0,70	0,70	0,70	1,05	1,20	1,36	1,52
1000	1,00	1,00	1,00	1,00	1,00	1,31	1,47	1,63	1,80
500	1,40	1,40	1,40	1,40	1,40	1,93	2,08	2,22	2,37
100	1,80	1,80	1,80	1,80	1,80	2,60	2,70	2,83	2,95
50	1,90	1,90	1,90	1,90	1,90	2,95	3,13	3,31	3,40
10	2,00	2,00	2,00	2,00	2,00	3,62	3,70	3,80	3,84

DISCOUNTS

Qty	1+	2+	4+	10+
Disc.	-10%	-10%	-15%	On request

Part number	Ratio	Type	Input	Efficiency at 1000 rpm	Max. input speed (rpm)	Reflected inertia at input (kg.m ²)	Static self-locking output	Stock*	Price each
E20-1	1:1	Helical	A	88%	4000	$3,762 \times 10^{-6}$	NO	✓	535,64 €
E20-2	2:1	Helical	A	86%	4000	$2,349 \times 10^{-6}$	NO	-	535,64 €
E20-3	3:1	Helical	A	85%	4000	$2,011 \times 10^{-6}$	NO	-	535,64 €
E20-4	4:1	Helical	A	84%	4000	$1,986 \times 10^{-6}$	NO	-	535,64 €
E20-5	5:1	Helical	A	80%	4000	$1,544 \times 10^{-6}$	NO	-	535,64 €
E20-8	8:1	Worm+wheel	A	80%	2000	$1,622 \times 10^{-6}$	NO	-	535,64 €
E20-10	10:1	Worm+wheel	A	73%	2000	$1,609 \times 10^{-6}$	NO	-	535,64 €
E20-20	20:1	Worm+wheel	A	67%	2000	$1,593 \times 10^{-6}$	YES	✓	535,64 €
E20-40	40:1	Worm+wheel	A	60%	2000	$1,589 \times 10^{-6}$	YES	✓	535,64 €
E20-SP	1:1 - 40:1	Ratio from 1:1 to 40:1							- On request
E20-SPA	1:1 - 40:1	Reduced output backlash $\leq 30'$							On request
E20-SPLH	1:1 - 40:1	Left handed							On request

* Depending on availability - Dimensions in mm

Torque up to 9Nm



Torque up to 20Nm


E40

- Ratios from 1:1 to 40:1
- Single piece construction
- Output backlash $\leq 45'$ (0,75°)
- Max. input speed up to 3000 rpm
- Materials:

Casina: anodised aluminium

gears and worms: case-hardened steel

- Ratios 1:1 to 5:1, input and output: case-hardened steel
 - Ratios $\geq 8:1$, input: case-hardened steel
output: bronze
 - Weight: 1.67 kg
- 
- Technical drawing of a shaft with a central section of length 72 mm and diameter 4.5 mm, and two end sections of length 63 mm and diameter 4.5 mm.




Options

- Can be modified your specification

Accessories

- Input or output shafts
E-X and E-DX
(tome 2 p.183)



OUTPUT TORQUE (Nm values given as a guide only)

Ratios		1:1	2:1	3:1	4:1	5:1	8:1	10:1	20:1	40:1
INPUT SPEED (RPM)	3000	2.3	2.3	2.3	2.3	2.3	-	-	-	-
	2000	2.8	2.8	2.8	2.8	2.8	-	-	-	-
	1000	3.8	3.8	3.8	3.8	3.8	7.3	8.0	8.8	9.7
	500	5.0	5.0	5.0	5.0	5.0	10.7	11.3	12.2	13.1
	100	8.0	8.0	8.0	8.0	8.0	14.2	15.0	15.8	16.7
	50	9.0	9.0	9.0	9.0	9.0	17.1	17.3	17.7	18.2
	10	10.0	10.0	10.0	10.0	10.0	19.5	19.6	19.8	20.0

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-5%	On request

[illegible]

*Depending on availability - Dimensions in mm

Right angle helical gearbox



E50

Torque up to 41Nm

- Ratios from 1:1 to 40:1
- Single piece construction
- Output backlash $\leq 45'$ (0,75°)
- Max. input speed up to 3000 rpm
- Materials:

Casing: anodised aluminium
gears and worms: case-hardened steel


- Ratios 1:1 to 5:1, input and output: case-hardened steel
- Ratios $\geq 8:1$, input: case-hardened steel, output: bronze
- Weight: 3.18 kg

Options

- Can be modified to your specifications

Accessories

- Input or output shafts
- E-X and E-DX (tome 2 p.183)



OUTPUT TORQUE (Nm values given as a guide only)

Ratios	1:1	2:1	3:1	4:1	5:1	8:1	10:1	20:1	40:1
3000	3,0	3,0	3,0	3,0	3,0	-	-	-	-
2000	4,0	4,0	4,0	4,0	4,0	-	-	-	-
1000	6,0	6,0	6,0	6,0	6,0	11,3	13,0	15,0	17,0
500	8,0	8,0	8,0	8,0	8,0	18,0	20,0	21,0	23,0
100	12,0	12,0	12,0	12,0	12,0	25,0	26,0	28,0	30,0
50	14,0	14,0	14,0	14,0	14,0	31,0	31,0	32,0	33,0
10	16,0	16,0	16,0	16,0	16,0	40,0	40,0	41,0	41,0

DISCOUNTS

Qty	1+	2+	4+
Disc.	List -5%	On request	On request

Part number	Ratio	Type	Input	Efficiency at 1000 rpm	Max. input speed (rpm)	Reflected inertia at input (kg.m ²)	Static self-locking output	Stock	Price each
E50-1	1:1	Helical	B	93%	3000	4,585 x 10 ⁻⁴	NO	✓	998,67 €
E50-2	2:1	Helical	A	91%	3000	2,240 x 10 ⁻⁴	NO	✓	998,67 €
E50-3	3:1	Helical	A	90%	3000	1,759 x 10 ⁻⁴	NO	✓	998,67 €
E50-4	4:1	Helical	A	89%	3000	1,924 x 10 ⁻⁴	NO	✓	998,67 €
E50-5	5:1	Helical	A	80%	3000	1,920 x 10 ⁻⁴	NO	✓	998,67 €
E50-8	8:1	Worm+wheel	A	80%	1000	1,489 x 10 ⁻⁴	NO	✓	998,67 €
E50-10	10:1	Worm+wheel	A	73%	1000	1,496 x 10 ⁻⁴	NO	-	998,67 €
E50-20	20:1	Worm+wheel	A	67%	1000	1,463 x 10 ⁻⁴	YES	✓	998,67 €
E50-40	40:1	Worm+wheel	A	60%	1000	1,455 x 10 ⁻⁴	YES	✓	998,67 €
E50-SP	1:1 - 40:1	Ratio from 1:1 to 40:1							On request
E50-SPA	1:1 - 40:1	Reduced output backlash $\leq 30'$							On request
E50-SPLH	1:1 - 40:1	Left handed							On request

*Depending on availability - Dimensions in mm


Right angle helical gearbox



E60

Torque up to 62Nm

- Ratios from 1:1 to 40:1
- Single piece construction
- Output backlash $\leq 45'$ (0,75°)
- Max. input speed up to 3000 rpm
- Materials:
 - casing: anodised aluminium
 - gears and worms: case-hardened steel
- Ratios 1:1 to 5:1, input and output: case-hardened steel
- Ratios $\geq 8:1$, input: case-hardened steel, output: bronze
- Weight: 5.50 kg




Options

- Can be modified to your specifications

Accessories

- Input and output shafts E-X and E-DX (tome 2 p.183)



OUTPUT TORQUE (Nm values given as a guide only)

Ratios	1:1	2:1	3:1	4:1	5:1	8:1	10:1	20:1	40:1
3000	4,5	4,5	4,5	4,5	4,5	-	-	-	-
2000	5,5	5,5	5,5	5,5	5,5	-	-	-	-
1000	8,0	8,0	8,0	8,0	8,0	17,8	21,3	22,0	24,0
500	10,0	10,0	10,0	10,0	10,0	27,0	29,0	31,0	34,0
100	16,0	16,0	16,0	16,0	16,0	37,0	40,2	42,0	44,0
50	20,0	20,0	20,0	20,0	20,0	48,0	49,0	50,0	51,0
10	24,0	24,0	24,0	24,0	24,0	60,0	60,0	61,0	62,0

DISCOUNTS


Qty	1+	2+	4+
Disc.	List	-5%	On request

Part number	Ratio	Type	Input	Efficiency at 1000 rpm	Max. input speed (rpm)	Reflected inertia at input (kg.m ²)	Static self-locking output	Stock*	Price each
E60-1	1:1	Helical	B	94%	3000	1,319 x 10 ⁻³	NO	✓	1 203,93 €
E60-2	2:1	Helical	A	92%	3000	6,507 x 10 ⁻⁴	NO	-	1 203,93 €
E60-3	3:1	Helical	A	91%	3000	5,111 x 10 ⁻⁴	NO	-	1 203,93 €
E60-4	4:1	Helical	A	90%	3000	5,543 x 10 ⁻⁴	NO	✓	1 203,93 €
E60-5	5:1	Helical	A	80%	3000	5,489 x 10 ⁻⁴	NO	-	1 203,93 €
E60-8	8:1	Worm+wheel	A	80%	1000	4,951 x 10 ⁻⁴	NO	✓	1 203,93 €
E60-10	10:1	Worm+wheel	A	73%	1000	4,911 x 10 ⁻⁴	NO	✓	1 203,93 €
E60-20	20:1	Worm+wheel	A	67%	1000	4,859 x 10 ⁻⁴	YES	✓	1 203,93 €
E60-40	40:1	Worm+wheel	A	60%	1000	4,846 x 10 ⁻⁴	YES	✓	1 203,93 €
E60-SP	1:1 - 40:1	Ratio from 1:1 to 40:1							On request
E60-SPA	1:1 - 40:1	Reduced output backlash $\leq 30'$							On request
E60-SPLH	1:1 - 40:1	Left handed							On request


* Depending on availability - Dimensions in mm

Torque up to 24Nm

- Large bore



- Can be modified to your specifications



Ratios		1:1	2:1	3:1
INPUT SPEED (RPM)	3000	4,5	4,5	4,5
	2000	5,5	5,5	5,5
	1000	8,0	8,0	8,0
	500	10,0	10,0	10,0
	200	16,0	16,0	16,0
	100	20,0	20,0	20,0
	50	24,0	24,0	24,0

Qty	1+	2+	4+
Disc.	List	-5%	On request


[illegible]

*Depending on availability - Dimensions in mm


- Optional accessory for adding outputs shafts to E series gearboxes

Composition

- Single sided shaft kit E-X: shaft in stainless steel 303, 2 steel keys and 2 steel circlips
- Double shaft kit E-DX: stainless steel 303 shaft, 3 steel keys and 2 steel circlips




Single sided shaft E-X



Double sided shaft E-DX



Single sided



Double sided

Assembly examples

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request


Part number	For gearbox	ØD	O/L	M	P	X	L	K	Price each 1 to 5
Single sided									
E20-X	E20	6	68,80	40	41,60	3,00	25	K2 x 22	34,21 €
E30-X	E30	10	98,60	54	56,20	3,50	40	K3 x 20	40,48 €
E40-X	E40	15	127,10	72	74,20	4,00	50	K5 x 30	49,24 €
E50-X	E50	20	153,80	88	90,60	4,50	60	K6 x 32	57,24 €
E60-X	E60	25	182,30	106	108,60	5,00	70	K8 x 40	59,29 €
Double sided									
E20-DX	E20	6	91,60	40	41,60	3,00	25	K2 x 22	44,14 €
E30-DX	E30	10	136,20	54	56,20	3,50	40	K3 x 20	50,81 €
E40-DX	E40	15	174,20	72	74,20	4,00	50	K5 x 30	59,11 €
E50-DX	E50	20	210,60	88	90,60	4,50	60	K6 x 32	68,69 €
E60-DX	E60	25	248,60	106	108,60	5,00	70	K8 x 40	80,09 €

Dimensions in mm



Crossed axis gearboxes

Technical information


- **Speed ratio:** from 1:1 to 40:1
- **Materials :**
 - casing anodised aluminium
 - gears in case hardened
(ratio >8 : output aluminium bronze)
- **Max. speed:** 3000 to 4000 rpm at input depending on model
- **Backlash(output):** $\leq 45'$ ($0,75^\circ$)
($\leq 0^\circ 30'$ optional)
- **Lubrication:** greased for life
(Shell Gadus S2 V220AD 2)
- **Guarantee:** 13 months
- **Steel bearing with single ball**
- **Lubrication temperature :**
max operating 60°C
- **Cooling** may be needed dependent on application



Typical application



Left handed teeth (LH)



Right handed teeth (RH)

ADMISSIBLE LOADS

Part number	Distance 'X' (mm)	Radial load (N)	Axial load (N)
E15	6	150	100
E20	6	150	100
E30	10	200	150
E40	12	400	300
E50	20	600	400
E60	25	800	500
E60B	25	800	500

Data given based on input speed of 1,000 rpm.
values given as an indication only.

