

Telescopic universal joint **stainless steel**



CTss

Low duty

- Standard series stainless steel version

- Plain bearings
- Max. misalignment angle 45°

- Material:

- Stainless steel 304
- Maximum speed 800 rpm
- Transmissible torque, see universal joint JCD (tome 2 p.85)

Applications


- Pharmaceutical and food industries

Accessory

- Don't forget the cover trim M (tome 2 p.92)



Stainless steel



Modifiable bore



DISCOUNTS

Qty	1+	2+	4+
Disc. Price	-15%	On request	

Part number	L min/ max	ØA	ØD	L1	L2	B	Stroke	E	F	ØDt	Price each
CT10-210/230/SS	210/230	10	22	76	25	30	20	11	14	21,2	345,80 €
CT10-220/250/SS	220/250	10	22	76	25	30	30	11	14	21,2	345,80 €
CT10-240/290/SS	240/290	10	22	76	25	30	50	11	14	21,2	345,80 €
CT10-260/300/SS	260/300	10	22	76	25	30	40	11	14	21,2	345,80 €
CT10-280/370/SS	280/370	10	22	76	25	30	90	11	14	21,2	345,80 €
CT12-220/230/SS	220/230	12	25	86	29	35	10	13	16	26,5	359,64 €
CT12-230/250/SS	230/250	12	25	86	29	35	20	13	16	26,5	359,63 €
CT12-250/290/SS	250/290	12	25	86	29	35	40	13	16	26,5	359,64 €
CT12-290/370/SS	290/370	12	25	86	29	35	80	13	16	26,5	359,63 €
CT12-330/450/SS	330/450	12	25	86	29	35	120	13	16	26,5	359,64 €
CT14-240/260/SS	240/260	14	29	90	30	35	20	13	16	26,5	374,13 €
CT14-260/300/SS	260/300	14	29	90	30	35	40	13	16	26,5	374,13 €
CT14-280/340/SS	280/340	14	29	90	30	35	60	13	16	26,5	374,13 €
CT14-320/420/SS	320/420	14	29	90	30	35	100	13	16	26,5	374,13 €
CT14-380/500/SS	380/500	14	29	90	30	35	120	13	16	26,5	374,13 €
CT14-440/600/SS	440/600	14	29	90	30	35	160	13	16	26,5	374,13 €

Dimensions in mm

DISCOUNTS

Qty	1+	2+	4+
Disc.	Price -15%		On request

Part number	L min/ max	ØA	ØD	L1	L2	B	Stroke	E	F	ØDt	Price each
CT16-250/270/SS	250/270	16	32	95	30	40	20	16	20	32,5	381,24 €
CT16-260/290/SS	260/290	16	32	95	30	40	30	16	20	32,5	381,23 €
CT16-290/350/SS	290/350	16	32	95	30	40	60	16	20	32,5	381,23 €
CT16-330/430/SS	330/430	16	32	95	30	40	100	16	20	32,5	381,23 €
CT16-400/570/SS	400/570	16	32	95	30	40	170	16	20	32,5	381,23 €
CT16-500/720/SS	500/720	16	32	95	30	40	220	16	20	32,5	381,23 €
CT18-270/280/SS	270/280	18	37	108	35	40	10	16	20	32,5	431,55 €
CT18-280/300/SS	280/300	18	37	108	35	40	20	16	20	32,5	431,55 €
CT18-300/340/SS	300/340	18	37	108	35	40	40	16	20	32,5	431,55 €
CT18-330/400/SS	330/400	18	37	108	35	40	70	16	20	32,5	431,55 €
CT18-380/500/SS	380/500	18	37	108	35	40	120	16	20	32,5	431,55 €
CT18-450/620/SS	450/620	18	37	108	35	40	170	16	20	32,5	431,55 €
CT20-280/290/SS	280/290	20	40	108	32	48	10	18	22	41,5	438,79 €
CT20-290/310/SS	290/310	20	40	108	32	48	20	18	22	41,5	438,79 €
CT20-310/350/SS	310/350	20	40	108	32	48	40	18	22	41,5	438,79 €
CT20-350/430/SS	350/430	20	40	108	32	48	80	18	22	41,5	438,81 €
CT20-400/530/SS	400/530	20	40	108	32	48	130	18	22	41,5	438,79 €
CT20-500/730/SS	500/730	20	40	108	32	48	230	18	22	41,5	438,79 €
CT20-550/830/SS	550/830	20	40	108	32	48	280	18	22	41,5	438,79 €
CT22-320/330/SS	320/330	22	47	127	38	48	10	21	25	47,5	553,29 €
CT22-330/350/SS	330/350	22	47	127	38	48	20	21	25	47,5	553,29 €
CT22-350/390/SS	350/390	22	47	127	38	48	40	21	25	47,5	553,29 €
CT22-390/470/SS	390/470	22	47	127	38	48	80	21	25	47,5	553,29 €
CT22-460/600/SS	460/600	22	47	127	38	48	140	21	25	47,5	553,29 €
CT22-560/800/SS	560/800	22	47	127	38	48	240	21	25	47,5	553,29 €
CT25-340/350/SS	340/350	25	50	140	44	48	10	23	28	47,5	553,29 €
CT25-350/370/SS	350/370	25	50	140	44	48	20	23	28	47,5	553,29 €
CT25-370/400/SS	370/400	25	50	140	44	48	30	23	28	47,5	553,29 €
CT25-400/460/SS	400/460	25	50	140	44	48	60	23	28	47,5	553,29 €
CT25-450/550/SS	450/550	25	50	140	44	48	100	23	28	47,5	553,29 €
CT25-500/650/SS	500/650	25	50	140	44	48	150	23	28	47,5	553,29 €
CT25-600/850/SS	600/850	25	50	140	44	48	250	23	28	47,5	553,29 €
CT30-420/430/SS	420/430	30	58	178	58	48	10	26	32	60	856,28 €
CT30-430/450/SS	430/450	30	58	178	58	48	20	26	32	60	856,28 €
CT30-450/490/SS	450/490	30	58	178	58	48	40	26	32	60	856,28 €
CT30-490/570/SS	490/570	30	58	178	58	48	80	26	32	60	856,28 €
CT30-550/690/SS	550/690	30	58	178	58	48	140	26	32	60	856,28 €
CT30-650/890/SS	650/890	30	58	178	58	48	240	26	32	60	856,28 €

Dimensions in mm

Our other products



CHM63
Worm and wheel gear reducer, up to 196 Nm



PARF110
Pressed steel base rigid foot, Swivelling Ø110



HSE-HSB
Hexagonal spacer, Steel



SLB
Indexing plunger, steel class 5.8



PW_PWG05
Wheel - precision range, Bronze



CHAupa
Front hinge, 270°



TFR
Rigid manual tensioner, Fixed



EMS
Stainless steel knurled thumb nut, Knurled



BPHF
Ball transfer unit push fit, Heavy



SLVHlok
Vertical toggle clamp, Vertical toggle clamp / horizontal foot



CHAu
Screwed hinge, 270°




T5M T10M
T type timing belt per metre, T5 Steel cored polyurethane

Complementary products



M
Bellows cover, Accessory:



CT
Telescopic universal joint, Normal duty



JCSs
Single stainless steel universal joint, Low duty



JCDs
Double universal joint - Stainless steel, Low duty