


## Ratio 2:1

## Steel 60C40

- **Module 0.8 to 6**
- Pressure angle 20°
- Teeth: **GLEASON**
- Material: Steel 60C40
- Two gears are required to make a pair



**N.B Torque ratings can be doubled by heat treatment**

TORQUE and POWER INDICATION	For 20 teeth at 1000 rpm				
	MOD 2,5	MOD 2	MOD 1,5	MOD 1	MOD 0,8
Torque (Nm)	4,30	2,20	0,94	0,57	0,14
Power (kW)	0,455	0,231	0,097	0,03	0,015

### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Teeth		ØP	E	ØD	ØA	ØM	F	G	H	ØR	T	Stock*	Price each 1 to 5
	Z	Mod												
DB0.8-15	15	0,8	12,00	20,0	13,93	6	10	11,90	7,50	4,02	M3	3,5	✓	32,56 €
DB0.8-30	30		24,00	14,0	24,64	8	20	10,08	5,50	4,02	M3	3,5	✓	38,39 €
DB1-15	15	1,0	15,00	24,0	17,42	8	14	13,87	8,76	5,03	M4	4,0	✓	36,92 €
DB1-30	30		30,00	18,0	30,58	10	25	13,11	7,00	5,03	M4	4,0	✓	45,38 €
DB1.5-15	15	1,5	22,50	35,0	26,12	10	21	19,84	12,13	7,55	M4	5,0	✓	40,24 €
DB1.5-30	30		45,00	27,0	45,87	10	30	19,66	11,00	7,55	M4	5,0	✓	51,56 €
DB2-15	15	2,0	30,00	45,0	34,83	12	28	24,76	14,86	10,06	M5	7,5	✓	44,52 €
DB2-30	30		60,00	35,0	61,16	12	40	25,21	14,00	10,06	M5	8,0	✓	61,78 €
DB2.5-15	15	2,5	37,50	54,0	43,54	15	32	29,51	16,51	13,53	M5	8,0	✓	60,93 €
DB2.5-30	30		75,00	41,5	76,45	15	50	29,31	13,31	13,53	M5	7,0	✓	76,98 €

\*Depending on availability - Dimensions in mm

## Our other products




BPF  
Sheet steel flanged bearing for light loads, Sheet steel



HTD5M\_25  
HTD Heavy duty timing pulley, HTD5 Aluminium



INS\_BR  
Self tapping brass insert, Brass



T5courroie  
T type timing belt, T5 Steel cored polyurethane



JCDss  
Double universal joint - Stainless steel, Low duty




ESCON  
Speed controller 5A accessories, Kit of 4 cables for DC motor



NK40  
Drylin®N miniature guiding system, Width 40 mm



NPTF30  
Spacer for tube carrier, Fixing accessory Ø14 to Ø20



RPP  
Connecting plate for RPP type timing belts,



PVL  
Small lobed handle, Polyamide



NK17  
Drylin®N miniature guiding system, Width 17 mm



LVT  
Miniatur motorised actuator 4A, 4 amperes

Complementary products