

- **Indicator with an external sensor**
- Resolution: 0.1mm
- Max speed: 2.5m/s
- Display range: -99999 to 99999
- Display: LCD, character height 7.5mm
- Max distance between sensor and band: 1mm
- 3 button tactile keypad
- Sensor IP rating: IP57
- Indicator IP protection: IP54
- Working temperature: 0 to 50°C
- Relative humidity: 35-85%
- EMC protection: 2004/108/EC
- Power supply: ½AA 3.6B battery (Lithium-thionyl chloride)
- Battery life: Approx 4 years
- Material:

Sensor: Black anodised aluminium


Display housing: Plastic

NEW!



Parameters

- Reset/preset, absolute/incremental, mm/inch/degrees, 3 origin points



DISCOUNTS

Qty	1+	3+
Disc	List	On request

Part number	View	Length of sensor (mm)	Price each 1 to 2
F7-E-A-500	A	500	378,94 €
F7-E-A-1000	A	1000	378,94 €
F7-E-A-3000	A	3000	401,27 €
F7-E-A-5000	A	5000	423,60 €
F7-E-B-500	B	500	378,94 €
F7-E-B-1000	B	1000	378,94 €
F7-E-B-3000	B	3000	401,27 €
F7-E-B-5000	B	5000	423,60 €

Dimensions in mm

Our other products



MSP19

Masterplate® glueable insert
Ø19/Ø20, Cylindrical with nut



CDP

Flanged drill bushing, Steel



UGH16

H Type Guide units, For Ø12 and Ø16 actuators



BOX-TOR-DRING

Box set of Nitrile O-rings NBR90Sh A, Flange seals



MRASSeco

Low cost stainless steel quick link, Stainless steel



CHTRP

Single and dual output gearboxes, Up to 87,3 Nm



RTL450

Self-centering locking assembly, High torque



AT10-50ECO

AT type timing pulley, Economy range - AT10 aluminium



PLM-20SC

Cylindrical magnet, Cylindrical magnet



PCS_PA6

Plastic sprocket, 9.525mm (DIN 06B-1)



GPLss

Brush, stainless steel



BPP

Pressed steel flanged bearing for light loads, Sheet steel

Complementary products



F7-P-AM

Multifunction display, Magnetic band



F7-P-AM

Multifunction display, Magnetic ring