Suction cup, 2.5 bellows



DCG

For uneven and curved surfaces

- Suction cup to lift and move objects


- Materials:

nitrile (NBR): black color, silicone (SI): translucent, natural rubber (NR) grey color

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height







50+ 100+ 150+

DISCOUNTS

silicone

200+

DCG07C to DCG25		DCG30 to DCG60			Disc. List -5% -10% -15% On request		
Part number	ØD	н	Ød	А	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	- - CTM10M5		4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0			3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0			4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34		-	4,61 €
DCG30-NBR	32,0	37,5	8,0	23,0	SCR30M6	-	5,00€
DCG40-NBR	42,0	46,0	8,0	24,0			5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5		5,40 €
DCG10-SI	9,0	15,0	5,0	12,0			4,78 €
DCG15-SI	15,2	22,0	5,0	12,0			5,40 €
DCG18-SI	17,5	23,0	5,0	12,0			5,40 €
DCG20-SI	20,0	23,0	5,0	13,0			5,60 €
DCG25-SI	25,0	33,0	4,5	19,34		V	5,60 €
DCG30-SI	32,0	37,5	8,0	23,0	SCR30M6		6,19€
DCG40-SI	42,0	46,0	8,0	24,0			6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5		3,56 €
DCG10-NR	9,0	15,0	5,0	12,0			3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34		-	4,61 €
DCG30-NR	32,0	37,5	8,0	23,0	SCR30M6	-	5,00€
DCG40-NR	42,0	46,0	8,0	24,0		-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		V	8,49 €

^{*}Depending on availability - Dimensions in mm



Our other products



Front hinge, 270°



Masterplate® glueable insert Ø19, Cylindrical with tapped insert



Right angle helical reducers, from 4.50 to 24 Nm



Cylindrical spacer, Thermoplastic



Locking bolt, with T handle



Wear strip for slat top chain, Z profile to be filled



Rotex®, jaw coupling, cast iron



Standard stainless steel profile, 45 x 45 mm



Motor-gearbox 12V and 24V DC, from 4 to



Parallel axis helical gear, Machined plastic



Eye bolt stainless steel, Stainless steel



2 part rigid shaft clamp, Clamping jaw

Complementary products



Suction cup threaded insert, Insert for suction cup - Tread click-in



Suction cup threaded insert, Insert for suction cup - Socket screw