

# Suction cup, 2.5 bellows



## DCG

For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:



nitrile (NBR) : black color, silicone (SI) : translucent, natural rubber (NR) grey color



### Uses

- For moving parts with irregular or curved surfaces

- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

### DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
<b>Nitrile</b>							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34		-	4,61 €
DCG30-NBR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NBR	42,0	46,0	8,0	24,0	SCR30M6	-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
<b>Silicone</b>							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34		✓	5,60 €
DCG30-SI	32,0	37,5	8,0	23,0		✓	6,19 €
DCG40-SI	42,0	46,0	8,0	24,0	SCR30M6	✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
<b>Natural rubber</b>							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34		-	4,61 €
DCG30-NR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NR	42,0	46,0	8,0	24,0	SCR30M6	-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

\*Depending on availability - Dimensions in mm

## Our other products



PO  
Pull handle - Multi-sector, Tapped recessed insert



PGT  
Sliding profile, Sliding panel support



PSG2S  
Spur gear - precision range, Stainless steel 316



MSP38  
Masterplate® glueable insert Ø38, Cylindrical Ø38 with threaded s...



CLSCLP  
Clevis components, short version, Steel - Short range



HTD14M\_85  
HTD Heavy duty timing pulley, HTD14 Steel



BPFss  
Pressed stainless steel flange bearing, Stainless steel



PTA80ssEB  
Articulated foot with sheet metal base Ø80, 10000N




CHB  
Double output shaft, For CHB gearbox



BEAB  
Knob star grip antibacterial, Star,



FF30  
Offset spur gear reducer, from 21.50



B  
Steel bevel gear, 1:1

## Complementary products



SCR  
Suction cup threaded insert, Insert for suction cup - Socket screw



TM\_CTM\_CTF  
Suction cup threaded insert, Insert for suction cup - Tread click-in