

Suction cup, 2.5 bellows



DCG

For uneven and curved surfaces

- Suction cup to lift and move objects

- Materials:

nitrile (NBR) : black color, silicone (SI) : translucent,
natural rubber (NR) grey color

Natural
rubber



Nitrile



Silicone

Uses

- For moving parts with irregular or curved surfaces
- These bellows allow for a more supple and faster grip, and also compensate for differences in height



DCG07C to DCG25

DCG30 to DCG60

DISCOUNTS

Qty	1+	50+	100+	150+	200+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	H	Ød	A	Corresponding thread insert	Stock*	Price each 1 to 49
Nitrile							
DCG07C-NBR	7,0	14,2	4,0	10,0	CTM10M5	-	4,24 €
DCG10-NBR	9,0	15,0	5,0	12,0		✓	3,56 €
DCG15-NBR	15,2	22,0	5,0	12,0		✓	4,42 €
DCG18-NBR	17,5	23,0	5,0	13,0		-	4,61 €
DCG20-NBR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NBR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NBR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NBR	42,0	46,0	8,0	24,0		-	5,18 €
DCG60-NBR	62,0	55,0	8,0	28,0		-	7,91 €
Silicone							
DCG07C-SI	7,0	14,2	4,0	10,0	CTM10M5	-	5,40 €
DCG10-SI	9,0	15,0	5,0	12,0		✓	4,78 €
DCG15-SI	15,2	22,0	5,0	12,0		✓	5,40 €
DCG18-SI	17,5	23,0	5,0	12,0		✓	5,40 €
DCG20-SI	20,0	23,0	5,0	13,0		✓	5,60 €
DCG25-SI	25,0	33,0	4,5	19,34	SCR30M6	✓	5,60 €
DCG30-SI	32,0	37,5	8,0	23,0		✓	6,19 €
DCG40-SI	42,0	46,0	8,0	24,0		✓	6,19 €
DCG60-SI	62,0	55,0	8,0	28,0		-	9,43 €
Natural rubber							
DCG07C-NR	7,0	14,2	4,0	10,0	CTM10M5	-	3,56 €
DCG10-NR	9,0	15,0	5,0	12,0		-	3,56 €
DCG15-NR	15,2	22,0	5,0	12,0		-	4,42 €
DCG18-NR	17,5	23,0	5,0	12,0		-	4,61 €
DCG20-NR	20,0	23,0	5,0	13,0		-	4,61 €
DCG25-NR	25,0	33,0	4,5	19,34	SCR30M6	-	4,61 €
DCG30-NR	32,0	37,5	8,0	23,0		-	5,00 €
DCG40-NR	42,0	46,0	8,0	24,0		-	5,78 €
DCG60-NR	62,0	55,0	8,0	28,0		✓	8,49 €

*Depending on availability - Dimensions in mm


Our other products



AT5courroie
AT type timing belt,
AT5 Steel cored
polyurethane



EPRC
High helix leadscrew,
Cylindrical nut - up to
40mm per rotation



PF20
Worm and wheel gear
reducer, up to 5 Nm



PRF-SMA
Closing system for
aluminium profile,
Easily adjustable lock



TCC_SS
Stainless steel rigging
screw (hook/hook),
Stainless steel



PAS
Pull handle,
Reinforced PA
thermoplastic



TBD
Manual leadscrew
table with opposing
threads, 2kg



DOMI30
Accessories, Plate




HLA28
Right angle spiro
bevel gearbox, Up to
182Nm



BH02
Single housed bearing
assembly, Bearing
secured with circlips



INSTool
Insertion tool for self
tapping inserts,
Insertion tool



M2
Worm and wheel set,
Machined plastic
(delrin)

Complementary products



SCR
Suction cup threaded
insert, Insert for
suction cup - Socket
screw



TM_CTM_CTF
Suction cup threaded
insert, Insert for
suction cup - Tread
click-in