



- Suitable for most applications due to the use of self lubricating bronze bearings in the end connectors
- Allows the driving and driven elements to be mounted apart
- Obstacles can be avoided, multiple bends possible
- Position of the driven element is no longer determined by the position of the driving equipment
- Output efficiency >95%
- Dampens vibration
- Woven wire flexible shaft
- Materials:
 - Wires: blackened XC25 steel
 - Sheath: PVC



standard end
(with 2 locknuts)



Dark grey areas are fixed parts.
Light grey areas are revolving parts.

Part number	ØC core	ØM	ØA	B	ØD	E	A/F	ØF	G	ØH	J	Screw
FDSQ4-L	3,80	M15x1,0	4	10	10,5	43	22	15,0	8	12,5	4	M3
FDSQ5-L	4,75	M18x1,0	5	16	14,0	50	24	18,0	12	15,5	4	M3
FDSQ6-L	6,35	M21x1,0	6	17	17,0	59	27	21,0	14	18,5	4	M4
FDSQ8-L	8,00	M22x1,5	8	23	17,5	63	30	22,0	17	18,5	4	M4
FDSQ9-L	9,52	M26,5x1,5	10	25	22,5	69	35	26,5	20	23,0	4	M5
FDSQ13-L	12,70	M29,5x1,5	15	31	25,0	84	36	29,5	24	26,0	4	M6


Dimensions in mm

Info.



- Replace the "L" in the part number by the length required and add the desired end (R: standard; S: optional)
E.g. **FDSQ4A-500RR**
- Steel core lubricated with oil
- For continuous use, the shaft should be lubricated every 3 months
- Flexible shaft can be removed by unscrewing the knurled part. Check the sealing before re-use
- Delivered pre-bored

NOTE: For assembly, the end must be drilled and pinned to the connected shaft. The set screw is only there for positioning. It does not allow torque to be transmitted.

BEND RADIUS
Radius = $\frac{a^2 + b^2}{4b}$ (mm)



Depending on the sense of shaft rotation, the braiding may be different.



"L" in part number refers to length, see **info**.

anti-clockwise	Part number bidirectional	clockwise	Price for 500 mm	Price for 1000 mm	Price for 1500 mm	Price for 2000 mm	Price for 2500 mm	Price for 3000 mm
FDSQ4A-L	FDSQ4B-L	FDSQ4C-L	On request	On request	On request	On request	On request	On request
FDSQ5A-L	FDSQ5B-L	FDSQ5C-L						
FDSQ6A-L	FDSQ6B-L	FDSQ6C-L						
FDSQ8A-L	FDSQ8B-L	FDSQ8C-L						
FDSQ9A-L	FDSQ9B-L	FDSQ9C-L						
FDSQ13A-L	FDSQ13B-L	FDSQ13C-L						

Dimensions in mm

Our other products



Connecting plate for T type timing belts, T10



PERIFLEX® elastic coupling, Complete coupling



Pull handle, Stainless steel



Clamp for aluminium profile, Clamp for profile



Knurled torque knobs - male, Knurled threaded torque



Joint for guiding profile, Rounded



Suction cup, 1.5 bellows, natural rubber



Hi-Klik™ indent hinge, Hi-Klik™ - Detent hinge



Ball and socket joint, Stainless steel



Stainless steel Clamping collar, Stainless steel



Worm - precision range, Stainless steel



Shaft for linear guides, Hardened ground steel

Complementary products



Flexible drive shaft, Masterflex® Steel, with PVC casing