


Masterflex® flexible shaft




FDSQ

Normal use

- Suitable for most applications due to the use of self lubricating bronze bearings in the end connectors
- Allows the driving and driven elements to be mounted apart
- Obstacles can be avoided, multiple bends possible
- Position of the driven element is no longer determined by the position of the driving equipment
- Output efficiency >95%
- Dampens vibration
- Woven wire flexible shaft
- Materials:
 - Wires: blackened XC25 steel
 - Sheath: PVC



standard end
(with 2 locknuts)



Dark grey areas are fixed parts.
Light grey areas are revolving parts.

Part number	ØC core	ØM	ØA	B	ØD	E	A/F	ØF	G	ØH	J	Screw
FDSQ4-L	3,80	M15x1,0	4	10	10,5	43	22	15,0	8	12,5	4	M3
FDSQ5-L	4,75	M18x1,0	5	16	14,0	50	24	18,0	12	15,5	4	M3
FDSQ6-L	6,35	M21x1,0	6	17	17,0	59	27	21,0	14	18,5	4	M4
FDSQ8-L	8,00	M22x1,5	8	23	17,5	63	30	22,0	17	18,5	4	M4
FDSQ9-L	9,52	M26,5x1,5	10	25	22,5	69	35	26,5	20	23,0	4	M5
FDSQ13-L	12,70	M29,5x1,5	15	31	25,0	84	36	29,5	24	26,0	4	M6


Dimensions in mm

Info.



- Replace the "L" in the part number by the length required and add the desired end (R: standard; S: optional)
E.g. **FDSQ4A-500RR**
- Steel core lubricated with oil
- For continuous use, the shaft should be lubricated every 3 months
- Flexible shaft can be removed by unscrewing the knurled part. Check the sealing before re-use
- Delivered pre-bored

NOTE: For assembly, the end must be drilled and pinned to the connected shaft. The set screw is only there for positioning. It does not allow torque to be transmitted.

BEND RADIUS
Radius = $\frac{a^2 + b^2}{4b}$ (mm)



Depending on the sense of shaft rotation, the braiding may be different.



"L" in part number refers to length, see info.

Part number			Price for	Price for	Price for	Price for	Price for	Price for
anti-clockwise	bidirectional	clockwise	500 mm	1000 mm	1500 mm	2000 mm	2500 mm	3000 mm
FDSQ4A-L	FDSQ4B-L	FDSQ4C-L	On request	On request	On request	On request	On request	On request
FDSQ5A-L	FDSQ5B-L	FDSQ5C-L						
FDSQ6A-L	FDSQ6B-L	FDSQ6C-L						
FDSQ8A-L	FDSQ8B-L	FDSQ8C-L						
FDSQ9A-L	FDSQ9B-L	FDSQ9C-L						
FDSQ13A-L	FDSQ13B-L	FDSQ13C-L						

Dimensions in mm

Our other products



T39_T49

Extension spring in metre length stainless steel, by the metre



MHPGR

Arm with folding rotating handle,



NSA

Adjustable clamp, Articulated



STRIP

Sealing brush strip, 3m length



CHALss

Piano hinge, Stainless steel



MAX26

Motor-gearbox 12V and 24V DC, from 0,075 to 0,6Nm



HTD3M_09

HTD Heavy duty timing pulley, HTD3 Aluminium



SHW

Plain washer, Steel



PRT

Rotary table iglidur®, Iglidur®, aluminium



MSP19

Masterplate® glueable insert Ø19,



HW_HT

Half-rail guide, Rail



PW_PWG3

Worm - precision range, Stainless steel

Complementary products



FDS

Flexible drive shaft, Masterflex® Steel, with PVC casing