



# Socket with protective insert

Hygienic Design® and Usit®

DEP-HD

## - Socket with protective plastic insert for mounting Hygienic Design® and Usit® products


### - Materials:

Socket: tool steel

Insert: special PETP


## Advantages

- 1/2" drive socket with a plastic insert to tighten and loosen screws and nuts in the Hygienic range. The plastic insert is made of special PETP and is FDA approved. The inserts are pressed into the socket by hand. Their special shape, combined with a clamping device, ensures optimal retention inside the socket.
- No special tools are required to replace worn plastic inserts.
- With a tightening torque (according to DIN standard for A4-70 screws and nuts, friction coefficient 0.12 $\mu$ ) the inserts plastic have a life span of up to 1,000 cycles or more.



□12,5(1/2")

DEP/HD socket



DEP/HD/INS insert

## DISCOUNTS

Qty	1+	5+	10+
Disc	Net	-5%	On request

Part N°	ØD	ØD1	L	T	SW	SW1	Suitable for hexagonal screw	Price each
								1 to 4
<b>Socket</b>								
DEP-11/HD	16,6	22	37,3	10,1	11	-	-	25,65 €
DEP-13/HD	19,1	22	37,3	10,6	13	-	-	25,52 €
DEP-16/HD	22,9	23,6	37,1	11,3	16	-	-	26,87 €
DEP-19/HD	26,6	23	37,0	13,2	19	-	-	27,77 €
DEP-21/HD	29,0	25	36,8	12,9	21	-	-	43,21 €
DEP-27/HD	35,2	25	44,4	18,1	27	-	-	51,06 €
<b>Protective insert</b>								
DEP-8/HD/INS	-	-	18,0	6	11	8	M5	8,45 €
DEP-10/HD/INS	-	-	19,5	10	13	10	M6	8,52 €
DEP-13/HD/INS	-	-	21,5	11	16	13	M8	9,35 €
DEP-16/HD/INS	-	-	22,0	13,5	19	16	M10	9,82 €
DEP-18/HD/INS	-	-	21,5	12	21	18	M12	10,16 €
DEP-24/HD/INS	-	-	26,5	18	27	24	M16	14,51 €

All dimensions in mm

0 825 88 6000

Service 0,15 € / min  
+ prix appel

Fax

cial2@hpceurope.com

HPC


SUPPLEMENT 2019

61

## Our other products



PM4  
Worm and wheel set,  
Machined plastic  
(delrin)



VKM  
Square steel nut,  
Steel - 1 thread



PX  
Optional output shaft  
stainless steel, P  
gearboxes double  
sided outp...



SSE  
Stainless steel  
spherical bearing,  
Stainless steel / PTFE



TBE16  
Economic mini-table  
with trapezoidal  
leadscrew, 5kg




PITAss  
Locking bolt, with T  
handle



PW\_PWG05  
Worm - precision  
range, Steel



BUH77  
Motor-gearbox 12V  
and 24V DC, from 0.1  
to 2 Nm



CHB  
Worm and wheel gear  
reducer, up to 73 Nm



CHAL3  
Piano hinge,  
Aluminium



ES  
Bipod support base,  
Plastic



M1  
Worm and wheel set,  
Non hardened steel

## Complementary products