



- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

Option

- Alternative number of teeth, up to 231



Torque and power indication			
For 50 teeth at 1000 rpm			
	20NCD2 Z10CNF18.09	20NCD2 hardened	brass fibre
Nm	1	5	0.54 0.450
kW	0.104	0.522	0.06 0.045



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Stock*	Price each 1 to 5	
						G	PG		G	PG
G0.7-9	9	7,00	8,40	8,40	4	0,004	0,003	-	22,05 €	22,05 €
G0.7-10	10	7,70	9,10	9,10	4	0,005	0,003	✓	22,05 €	22,05 €
G0.7-11	11	8,40	9,80	9,80	4	0,006	0,004	-	22,05 €	22,05 €
G0.7-12	12	8,40	9,80	9,80	5	0,006	0,005	-	22,05 €	22,05 €
G0.7-13	13	9,10	10,50	10,50	5	0,007	0,005	-	22,64 €	22,64 €
G0.7-15	15	10,50	11,90	11,90	5	0,009	0,006	✓	23,66 €	23,66 €
G0.7-18	18	12,60	14,00	12,00	5	0,011	0,008	-	25,51 €	25,51 €
G0.7-20	20	14,00	15,40	12,00	5	0,012	0,009	-	26,05 €	26,05 €
G0.7-24	24	16,80	18,20	12,00	5	0,015	0,012	-	27,10 €	27,10 €
G0.7-26	26	18,20	19,60	12,00	5	0,017	0,014	-	27,71 €	27,71 €
G0.7-28	28	19,60	21,00	12,00	5	0,019	0,016	-	28,07 €	28,07 €
G0.7-30	30	21,00	22,40	12,00	5	0,021	0,018	-	28,52 €	28,52 €
G0.7-35	35	24,50	25,90	16,00	6	0,031	0,025	-	28,77 €	28,77 €
G0.7-40	40	28,00	29,40	16,00	6	0,038	0,031	-	29,09 €	29,09 €
G0.7-42	42	29,40	30,80	16,00	6	0,040	0,034	-	29,25 €	29,25 €
G0.7-48	48	33,60	35,00	16,00	6	0,050	0,044	-	29,81 €	29,81 €
G0.7-50	50	35,00	36,40	16,00	6	0,053	0,047	✓	30,14 €	30,14 €
G0.7-60	60	42,00	43,40	16,00	6	0,073	0,067	-	31,43 €	31,43 €
G0.7-70	70	49,00	50,40	16,00	8	0,094	0,092	-	32,73 €	32,73 €
G0.7-76	76	53,20	54,60	16,00	8	0,109	0,107	-	34,47 €	34,47 €
G0.7-175	175	122,50	123,90	25,00	12	0,566	0,547	-	91,32 €	91,32 €

On request

Gears available up to this size

G0.7-198	198	138,60	140,00	Dimensions: contact us	On request
----------	-----	--------	--------	------------------------	------------

*Depending on availability - Dimensions in mm

Our other products




PLM-SC

Magnetic stud with central countersunk hole, With milled bore



PDM_PDV

Detectable plastic palm grip, by metal detectors



PO

Pull handle - Multi-sector, Smooth hole



NKX

Combined bearing without inner ring, Needle and ball bearings



MPB

Hexagonal spacer, Brass



PSG05HC

Skive hobbled spur gears - precision range, Case hardened steel 20NCD2




D19 D29

Compression springs in metre length stainless steel, by the metre



BLH20

Right angled gearbox, from 0.53 to 1.77



HCV

V-rail guidance Simple Select® system, on rail



RAS

90° ball and socket joints DIN71802, Stainless steel



DOMI120

Domino 120 adjustable slide, Slide DOMILINE 120 with



S_ZZ

Deep groove ball bearing, Stainless steel

Complementary products



G0

Steel spur gear, Steel 20NCD2



G0

Steel spur gear, Steel 20NCD2